

Product	Item Update Description
Armstrong Integrated Designer	Resolved - When loading profile on current quote results in error displayed
	Resolved - Error displayed when requesting ARM approval with using Armstrong Integrated Designer selection
	Updated - Tango name clarity (Incident #155442)
Boosters	Updated - VMS 5 models of DE 6800 shipment indicator set to 4 weeks (Incident #154420)
	Updated - 6800G Specification document [UK] (Incident #154487)
Control Systems	Resolved - DP Sensor pressure range resets to a blank selection within the IPS panel when "Validate All" is clicked on a quote (Incident #156361)
Fire Systems	Resolved - For the fuel tank selection option, inaccurate NFPA20 2022 outline displayed (Incident #151988)
	Resolved - During selection of Fire pump housing with diesel and electric fire pump, the rpm for the electric pump is inaccurately displayed (Incident #153910)
	Resolved - Error displayed when selection of Diesel pump with 3000GPM@152PSI (Incident #153275)
	Resolved - Error displayed when selecting replacement Listed Fire pump, driver and controller [Brazil Market]
	Resolved - Under certain scenarios, curve and data points inaccurately displayed below required duty point (Incident #156354)
	Updated - Vertical Turbine Fire pump lead time
	Updated - When selecting HSC 6x5x12F, Silencer Grade is now reflected as Industrial within output Submittal
General	Resolved - Under specific scenarios when place order is selected, system is not responsive (Incident #156736)
Packaged Systems	Resolved - When selecting ETO Packaged Systems, under certain scenarios, result in Error 500 displayed [UK Market]
Parts	Resolved - When selecting search within Parts Finder, serial number and items not displayed (Incident #147966)
Pumps	Added - Impeller V-cut data for new Medium Pumps 4300 6x6x9.5 Medium pump
	Added - Impeller V-cut for new Medium Pumps 6x6x9.5, 8x8x11.5B (Incident #154234)
	Resolved - Inaccurate Curve outline for Constant Speed 8x8x13 (200-300) (Incident #130540)
	Resolved - Design Envelope, 4380, 1.5x1.5x5, 5 hp motor, single is missing the drawing details (Incident #92078)
	Removed - Medium Pump models VIL 3x3x11.5 and VIL 8x8x14.5 (Incident #154586)
	Resolved - The price incorrectly reflects NCP for Conventional - Variable speed pumps with user supplied controls (Incident #150858)
	Resolved - When configuring VMS64 model replacement Jockey Pump, error displayed when selecting product from grid result
	Resolved - Inaccurate pricing listed within DEPM when fluid type is changed and Seal changed from C-SSC to SSC-SSC (Incident #154532)
	Resolved - Incorrect potable water option available for standard ductile iron DE pump selection (Incident #155594)
	Removed - Various DE Envelope products moved to Manual select option only (Incident #156069)
	Removed - Medium Pump models VIL 3x3x11.5 and VIL 8x8x14.5 (Incident #154586)
	Updated - DEPM and DEPM IVS submittal output document inclusion of Cooling option field (Incident #151277)
	Updated - Various product lead times updated [China and Asia Pacific Rim Markets] (Incident #153895)
Selection	Updated - Various product lead times updated [India Market] (Incident #153896)
Service	Added - Detail outline within Submittal when Pump Manager selected during Pump configuration (Incident #133587)
	Added - DE pumps above 7.5hp come standard with Smart Strat-up
	Added - "Service" verbiage to line description when Services are included in quote
	Added - IE4 motors to Replacement Motor Configurator (Incident #153304)
	Updated - Replacement configurator notification message (Incident #148408)
Shell & tube	Updated - The default value for the "Baffle Spacing" menu set to default to "Maximum allowable Baffle Spacing" instead of the current minimum value (Incident #148267)
Tank Heaters	Resolved - Unable to select 316SS tube material option (Incident #153321)