

Descriptor	Summary
Boosters	Added - Various 6800 DE Booster Envelopes to the selection grid (UK Market) (Incident #132217)
	Resolved - Inaccurate Curve data for Booster Envelope: VMS-40:02-2B (UK Market) (Incident #129778)
Circulators	Launched - Specific S&H Circulator models
Control Systems	Launched - New System Envelope models
	Updated - SE-F10.1 submittal IO details (Canada Market)
Fire Systems	Resolved - Jockey Pump submittal data sheet missing specific data (Middle East Market) (Incident #131503)
	Resolved - Incorrect voltage shown for Vibrant Jockey pump and Jockey Pump controller (Incident #132426)
	Resolved - 6x5x12MF Fire pump performance Curve Issue
	Updated - Standardized package pricing for Enclosed Fire Pump reducing NCPs
	Updated - Curve data for 8x6x15MF and 8x6x12.5HF
Pumps	Added - G30 Seal for 4300 (China Market) (Incident #60659)
	Added - Impeller selection various pump sizes 10x10x13 & 10x8x13 (US and Canada Markets)
	Launched - IE4 Efficiency option as non-NCP (IEC Markets)
	Removed - 3kW motor for 3ph/200-230V DEPM models (IEC Markets) (Incident #130977)
	Resolved - Inaccurate lead time for certain non-standard motors (Incident #129361)
	Resolved - Incorrect curve displayed DE - VIL 3X3X10 models
	Resolved - Not able to select VMS 64:02-1B (Incident #131135)
	Resolved - Quote auto updated in certain scenarios displays error
	Resolved - FTV certain model submittal incorrectly outlined as flanged instead of threaded (Incident #131916)
	Resolved - BEP% warning displayed (Incident #131582)
	Resolved - Error displayed during manual configuration selection of 1050 Circulator (Incident #132580)
	Resolved - Unable to select H54 Circulator with required specifications (Incident #86375)
	Resolved - Inaccurate Lead Time displayed with specific motor for Pump Model 4300 (Incident #132645)
	Resolved - Inaccurate Lead Time on specific DE and IVS pumps with motor size larger than 150hp (Incident #132542)
	Resolved - Error displayed when selecting DE IVS Sensorless pump in the grid results (NEMA Market)
	Updated - V-Cut Dimension values for certain Medium pumps, Tango pumps and ES models (Incident #131573)
	Updated - Place DE IVS 15-60hp models to manual select option (Incident #128627)
	Updated - Danfoss VFD enclosure rating for selective DE and CVS pumps (Incident #124634)
	Updated - Lead time for various pump models (India, Middle East & Africa Markets) (Incident #128189)
	Updated - TM65 report data
Updated - At70 seals with upgraded G30/G30P seals (DCR-2024-026)	
Service	Resolved - Error display while adding Service and Parts (UK Direct Market)
	Resolved - Issue in Motor Frame size (215TC & 254TC) configurator (Incident #127782)
	Resolved - Various motor not selectable for 4270 pump (Incident #130519)
	Updated - Pump motor size selection based on power supply selected (Incident #123777)