

Product	Summary
Boosters	Updated - 6800Q Submittal updated field wiring diagram (Incident #126565)
	Updated - 6800Q DE/DEPM Booster specification document available for download (Incident #126832)
	Added - 60 Hz Electrical Options to DE6800Q [Middle East/Africa/Asia Pacific Markets] [DCR-2024-018]
	Updated - 5psi inclusion for user input boost pressure [UK, China, Asia Pacific / India / Middle East Markets] (Incident #129799)
Control Systems	Added - SE-A10 & A20 and EE-W10 & W20 are to be added to the available range. (DCR-2024-020)
	Updated - SE-A10 Standby pump to total pump number logic
	Resolved - Panel dimension label accuracy
Fire Systems	Updated - Submittal drawing inconsistencies (Incident #75133)
	Added - Jockey Pump Parts Kits (4700 Pumps) under accessories tab [NEMA Market] (Incident #119031)
	Updated - LPC Jockey pressure from value
	Updated - Quote Report Battery Submittal (Incident #121706)
	Removed - Cummins Engine option under Vertical Turbine Fire Pump selection (Incident #123717)
	Resolved - NFPA Fire Systems error displayed when clicking required model from results page
	Updated - When switching selection from Critical to Industrial in the Exhaust System selection, pricing error in selection (Incident #123723)
	Resolved - FM Jockey pump selections - pump size and motor size are now visible
	Updated - Peak Power table for HSC 8x6x12.5HF
	Resolved - NFPA displays Attention Needed message after added to quote
Guidance	Notiifcation - When Replacement Drive is required, use the Design Envelop Drive configurator
OEM	Resolved - Getting Print Error for Medium Pumps ES 4200H [NEMA Market] (OEM Selection)
Order Submission	Updated- Special Shipping Instructions "Note" field outlines Call-Before_Shipping not longer offered
	Validated - Expedite Option for CustoeMr Service use only confirmed (Incident #130253)
	Update - ARM request workflow process
Parts	Updated - Motor/Drive replacement parts pricing list (Incident #127171)
	Resolved - Replacement motor (4700) source shows DBV & MTV as power supply- "Get Results" does not display for default voltages
	Resolved - Selecting replacement motor for a 4270 1.25x1x5 - 1.5hp 3600RPM unable to add to submittal (Incident #126997)
	Added - DE 6800Q Booster replacement drive [Asia Pacific / China / India / Middle East / Africa Markets] (DCR-2024-022)

Product	Summary
Pumps	ADEPT- Options - Pumpless motor, Bareshaftpump, Pump kit - Removal (Incident #118703)
	Resolved - Brazil Market pump configurator selection error (Incident #119315)
	Added - Siemens Motor option for Customer Choice Motor dropdown selection (Incident #119964)
	Resolved - Submittal output format inconsistencies (Incident #119918)
	Updated - Lead Time for 200-208V Induction Motors moved to 14 Weeks (Incident #125004)
	Medium Pump ES 6inch incorrect price displayed [IEC Markets(Except UK)]
	Updated - Various Pump model curve/part items/other
	Resolved - 4360 pump kit missing (Incident #127319)
	Updated - TM65 report data
	Added - Medium Pump ES 6inch manual selection
	Removed - FS2 from the S-25 AB selection [Canada / US Markets] (Incident #127845)
	Resolved - Error 500 for duty points on QVMS 10 60Hz 4700 - QVMS-10:07A - 2p - 3 kW - 10.2 m ³ /hr 54.1 m [Middle East / Asia Pacific Markets]
	Resolved - Error 500 displayed when changing from default voltwage to option voltasge option 4700 pump 60HZ [Middle East / Asia Pacific Markets]
	Updatefd - Coefficient and Peak Power table for 8x6x15MF
	Updated - Varous pumps inaccurate Operational Costs displayed
	Updated - X-Dimensions for New VILs CS 4x3x9, CS 4x3x10 & DE 4x3x9
Resolved - Startup and Commissioning cost showing within Subtotal cost. (Incident #116832)	
Updated - Smart Re-Commissioning submittal (Incident #89572)	
Shell & tube	Resolved - Shell and Tube Heat Exchangers E model, Steam Shell length showing inaccurate description [Canada Market] (Incident #119325)