ARMSTRONG

Descriptor	Summary
Boosters	Added - New range of 60 hp DE 6800G boosters (in 2 Pump, 3 Pump, 4 Pump, and 5 Pump configurations) using the VMS45:07B pumps series and associated options
	Addition - DE 6800Q option for dspace dependent on base selection [Asia Pacific Market] (Incident #126048)
	Disabled - DE 6900 selection [North America Market] (Incident #127040)
Expansion Systems	Resolved - Incorrect grid result on AST Models based on various operating range entered
Fire System	Updated - Lead Time for Eaton Controller with Enclosure option (Incident #123863)
	Resolved - NFPA DE Fire - 4700 - VMS15 is suffixed with B instead of [IEC Markets]
	Resolved - Error 500 displayed LPC Fire System - NA7030 NA3x2.5x10M-(JU4H-NL22 , JU4H-NL14)
	Resolved - Duty Point not accurate for depicted duty curve 8x5x11.5FM (Incident #125896)
	Resolved - LPC Pump Shaft DIA size not displayed on Quote and SOS reports (Incident #119212)
	Added - Pricing (GBP) for 250L,450L and 650L tank sizes (Incident #119562)
	Updated - Various Lead Times [All Markets except UK & India] (Incident #121511)
	Updated - Flange rating PN16 updated for various End Suction Unlisted Bare Shaft Fire Pumps (Incident #124613)
	Added - Retrofit bases option for JU4H and JU6H engines
	Updated - Update IE3 motors to IE4 motors to meet new EU Regulation
	Added - PLD-D Clarke diesel engines for HSC and ES fire pump
	Updated - Clarke diesel engine costs (Incident #126747)
	Updated - Fire Pump Controllers cost multipliers (Incident #126745)
	Resolved - Dimension of Fire Pumps missing (Incident #123303)
	Added - PLD Calculator link
General	Updated - ADEPT Quote landing page design
	Updated - Split the expedited lead time request into 2 boxes
Guidance	Added - Parts and IOM link included within ADEPT Support and Guidance menu
	Added - Highlighted Expedite for internal use only
	Added - Notice to Shipping Note field
iFMS	Resolved - Download Error for IFMS
OEM	Resolved - OEM Selection Error
Order Submission	Restored - Standard Consult Factory workflow
	Resolved - Error message displayed for ARM request [US Market]
Parts	Removed - Selection of Impeller based on parameters. Part numbers are available through Parts Finder (with serial number), Customer Service or after-sales service (Incident #114264)
Plate/Frame Heat Exchanger	Updated - PFX Configurator missing 350psi rating (Incident #125143)



Descriptor	Summary
Pumps	Validated - 4380 Lead Time accurate (Incident #122630)
	Updated - Lead Time for Compass R Residential Pumps [NEMA Market] (Incident #116645)
	Updated - Pacdor Motor size format for DE IVS 4302 (Incident #122269)
	Resolved - New Engine Grid Selections
	Resolved - Pricing error 6x6x13H Pump (Incident #126486)
	Disabled - 10x10x13 & 10x8x13 Pumps impeller trim above 13.188" (Incident #126298)
	Resolved - False NCP required for 4380 100-150 4p 1.1kW pump (Incident #127395)
	Resolved - During manual selection IEC Motor size is not updating on post select Screen for 4700 - QVMS- 03:36A , 4700-QVMS-150:05-2A
	Added - 380/3/60 & 380/3/50 Price Adjustment for DE – IVS offering (that uses induction motors) (Incident #117548)
	Updated - Turn Down Ratio drop down selection field to the numeric input for PRS-PumpSystem
	Re-instated -Manual selection for the Medium Pump ES 6inch (DCR-2024-011)
	Added - Constant speed VMS offering for IEC market
	Updated - Changes / Additions to TM65 report data
	Updated - E-3559 Gen5 DEPM Fuse listing (Incident #125158)
	Updated - LP for the DE IVS 4300/4380 Pumps [UK Market] (Incident #125768)
	Removed - Drip Pan option selection for the 4030 Pumps (Incident #125780)
	Removed - Bareshaft Pump option for VIL Pumps for NEMA Market (Incident #127606)
	Resolved - Duplicate data shows left window - 4700 series
Service	Updated - Report verbiage for Performance Upgrade Suite Pump Series list