



Product	Summary
Order Submission	Updated - ARM workflow (India market)
Boosters	Updated - Curve ID for the new DE Booster Model (UPS-340022-05D-3 Pumps-VMS-40:02-2B-11 kW)
	Resolved - Line Drawing is missing for the Booster model NVS-364022-03S
	Resolved - Booster models (VMS-64:01B , VMS-64:04B , VMS-64:05-2B) added to grid and E3776 document (NEMA Market)
	Resolved - Booster configured with header size equal to "NA" (Incident #124650)
	Updated - Booster submittals (Incident #116938)
	Updated - Submittal template and corrected Float Switch quantity (UK Market) (Incident #116940)
	Validated - 16bar Accumulator tank (UK Market)
	Added - Locally sourced Boosters item for all Booster models (Incident #120649)
	Updated - DE Booster 6800Q Submittal drawing (Incident #122029)
	Updated - AFS booster 11kW motor PN change from 74350151-081 to 74350051-381 (Incident #124716)
Expansion	Validated - "Expansion system" vessel selection options - (K1903/544 - Reflex DE 1000) (Incident #124377)
	Updated - Pressurization unit selection (Incident #118537)
Fire	Updated - Replacement Jockey Pump - 4700 - VMS15 updated suffix with B instead of C.
	Resolved - P.O. failer for speciofic SQJK Quote (Incident #118810)
	Resolved - E-Unit configured when bypass loop = "No" - pulling correct loop kit (Incident #122970)
	Validated - Selection issue with 6x5x12MF
	Added - 4x3x10PF VIL Fire pump (DCR-2024-008)
	Updated - Item updates for VIL/ES Lantern Ring Maintenance (Incident #122378)
	Resolved - 4x3x13M changed to End Suction instead of Horizontal Split Case (North America Region)
	Resolved - Adept selection error
Pumps	Resolved - Load profile changes not updated until cache is cleared
	Resolved - CIMCO/SQDOU008085_11 4360B configured without a motor (Incident #118912)
	Validated - Pump 6" Tangos & Suction Guides - List price is not accurate for selecting "Power supply" = 460/3/60 (NEMA Market)
	Resolved - Manual selection on motor issue
	Resolved - Line details for comprehensive extended warranty displaying wrong motor size
	Validated - Small Gen-5 packaging issues (Incident #124884)
	Updated - Shipment Indicator for DEPM – IVS (Incident #116041)
	Resolved - Order error (Incident #120218)
	Added - DEPM models in circulators (DCR-2024-007)
	Resolved - SQXN004575-4 - NCP (Incident #121134)
	Resolved - Buy American and Baldor option issues
	Added - Medium Pump ES 6-inch (DCR-2024-011)
	Updated - Retain 4700 PUMP Motor configurator data/matrix without B models (Incident #122311)
	Updated - TM65 report data
	Updated - Seal 975000-976 updated to use 975000-975 (Incident #122857)
	Corrected - Customized motor annex text for Ambient temp (Incident #123724)
	Added - Nameplate bracket: CS medium pump (Incident #123086)
Parts	Resolved - Error displayed for Med Pump 6" Tangos & Suction Guides when selecting service kit item "Left Shroud Parts Kit /Right Shroud Parts Kit" (All Markets)
	Updated - Promotion code validation (Regional)



Product	Summary
Services	Validated - Multiplier on connectivity kit (Incident #114591)
	Updated - Line details specifics for Smart Services
	Updated - Smart Services item descriptions and list details
	Updated - Performance Upgrade Suite verbiage (Incident #96499)
Accessories	Resolved - Suction Guide & Flow-Trex Valve name plate specs not matching with submittal (Incident #118508)
	Updated - Shipment Error for the model SG1210 - 516860-531 (UK market)