



Certificate of Compliance

This certificate is issued for the following:

**CENTRIFUGAL FIRE PUMPS
(IN-LINE TYPE)**

Prepared for:

**S.A. Armstrong Ltd.
23 Bertrand Ave
Scarborough, Ontario M1L2P3
Canada**

FM Approvals Class: 1371

The pumps listed herein are FM Approved as of December 17, 2013

To verify the future Approval status of these products, please refer to www.approvalguide.com

Said Approval is subject to satisfactory field performance, continuing Surveillance Audits, and strict conformity to the constructions as shown in the Approval Guide, an online resource of FM Approvals.

A handwritten signature in black ink, appearing to read 'Richard B. Dunne', is written over a white rectangular background.

Richard B. Dunne
Group Manager-Fire Protection
FM Approvals
1151 Boston-Providence Turnpike
Norwood, MA 02062

December 17, 2013

Date



Member of the FM Global Group



Certificate of Compliance

Product	Rated Capacity, (gal/min)	Rated Capacity, (dm ³ /min)	Rated Net Head at Rated Capacity, psi	Rated Net Head at Rated Capacity, kPa	Rated Speed, r/min
LA-F	50	189	40-92	275-630	2945
LA-F	50	189	40-135	275-930	3565
LA-F	75	284	40-91	275-625	2945
LA-F	75	284	40-134	275-920	3565
LA-F	100	378	40-120	275-825	3565
LA-F	200	757	40-84	275-575	2945
LA-F	200	757	40-123	275-845	3550
LA-F	250	947	40-82	275-565	2945
LA-F	250	947	40-122	275-840	3550
LA-F	300	1136	40-120	275-825	3550
LA-F	400	1515	40-91	276-627	2945
LA-F	400	1515	40-133	276-917	3550
LA-F	450	1705	40-132	276-910	3550
LA-F	500	1895	40-131	276-903	3550
LB-F	750	2840	77-115	530-790	3560
LY-F	750	2840	40-70	275-480	1780
8x8x13FM	1000	3785	40-67	275-460	1775
8x8x15FM	1500	5680	67-102	462-703	1780
8x8x15FM	1250	4730	71-104	490-717	1780
8x8x15FM	1000	3785	73-106	503-730	1780
8x8x15FM	1250	4730	46-70	317-482	1480
8x8x15FM	1000	3785	49-72	338-496	1480
8x8x16FM	1000	3785	56-68	385-470	1480
8x8x16FM	1000	3785	83-101	570-695	1780
8x8x16FM	1250	4730	52-64	360-440	1480
8x8x16FM	1250	4730	79-97	545-670	1780
8x8x16FM	1500	5680	74-92	510-635	1780
2x2x8FM	50	190	44-86	305-595	2945
2x2x8FM	75	285	44-86	305-595	2945
2x2x8FM	100	380	43-86	295-595	2945
2x2x8FM	50	190	61-122	420-840	3500
2x2x8FM	75	285	61-122	420-840	3500
2x2x8FM	100	380	61-122	420-840	3500
2x2x8FM	150	570	58-120	400-825	3500
3x3x8FM	200	755	43-83	295-570	2945



Member of the FM Global Group



Certificate of Compliance

Product	Rated Capacity, (gal/min)	Rated Capacity, (dm ³ /min)	Rated Net Head at Rated Capacity, psi	Rated Net Head at Rated Capacity, kPa	Rated Speed, r/min
3x3x8FM	250	945	42-83	290-570	2945
3x3x8FM	300	1135	40-82	275-565	2945
3x3x8FM	200	755	50-118	345-815	3500
3x3x8FM	250	945	48-118	330-815	3500
3x3x8FM	300	1135	45-118	310-815	3500
5x5x8FM	400	1515	54-105	370-725	3500
5x5x8FM	450	1705	52-104	360-715	3500
5x5x8FM	500	1895	50-103	345-710	3500



Member of the FM Global Group