

R M

400

860

912 OVER ALL

30

400 CRS

698 251 4.9 219 60 5.9 219 251 60 748 251 60 6.9 219 1.8 783 219 251 251 8.8 251 219 60 10.8 251 13.8 983 219 60

STARTING

CURRENT

MM

219

219

251

IF IN DOUBT ASK

PRESSURE PRESSURE

TEST

MAX BAR

WORKING

MAX BAR


3.9

VESSEL


SIZE

60

60



FLEXIBLE CONNECTORS OPTIONAL ONLY SUPPLIED WHEN ORDERED (2-PER SHEET)



NOTE:-

DETAIL A SCALE 1:4

\MAIN ISOLATOR SWITCH

VESSEL 60LT. WITH KIT IS CONNECTED HERE

- 1) MAIN POWER SUPPLY TO PANEL MUST BE SIZED TO COVER ALL PUMPS RUNNING AT THE SAME TIME
- 2) LARGE STORAGE VESSELS, IF ORDERED, WILL BE SUPPLIED LOOSE FOR POSITIONING FOR CLIENT TO SUIT THE AVAILABLE FLOOR SPACE. CLIENT IS TO PROVIDE A CONNECTION FROM THE VESSEL TO THE DELIVERY PIPEWORK ADJACENT TO THE SET ISOLATING AND DRAIN VALVES SHOULD BE FITTED IN THIS CONNECTION
- 3) 60 Lt TANK WILL BE SUPPLIED LOOSE AND SHOULD BE ASSEMBLED ON SITE
- 4) FLANGES ARE AVAILABLE BOTH IN 16 & 25 BAR VERSION
- 5) FOR STANCHION SELECTION USE DRAWING NO. PK14967

ITEM NO	DESCRIPTION	NO. OFF
1	BASE PLATE	1
2	BOLT - M12	12
3	WASHER - M12	12
4	CAGE NUT - M12	12
5	VMS PUMP	3
6	SUCTION/DISCHARGE MANIFOLD ASSY	2
7	ISOLATING VALVE 1 1/4"	6
8	NRV 1 1/4"	3
9	SUPPORT RIB	1
10	STANCHION	1
11	PRESSURE TRANSDUCER	1
12	PRESSURE GAUGE	1
13	FEMALE CROSS 1/2"	1
14	ISOLATING VALVE 1/2"	1
15	AIR VENT 1/4"	1
16	CONTROL PANEL	1
17	1/2" NIPPLE	3
18	1/2" x 1/4" REDUCING BUSH	3
19	BOLT - M10	9
20	WASHER - M10	9
21	NUT - M10	3
22	CAGE NUT - M10	6
23	1/2" T	1
24	END CAP	2

12

						PART No.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm	TVAVIC	DATE	MCTDO	NC I	
						JOB No.	WELD SYMBOLS TO BS 499 SURFACE FINISH SHOWN IN um.	DRAWN PRAKASH CHECKED	03/03/08 AK	MOIKO	NU	
						DESIGN No.	MACHINE WHERE SHOWN		TITLE:	0000 11140 0	EDIEO	
		LAST MODIFICA	TION DETAILS		PROPRIETARY AND CONFIDENTIAL	PATTERN No.	TO TOLERANCE ± 0.3	MFG APPR.		6800 HMP S		
-					THIS DRAWING IS THE PRIVATE	FILE NAME	DIMENSIONING AND TOLERANCING PER: BS 308	ENG APPR.		3PUMP SV04		
-					AND CONFIDENTIAL PROPERTY OF ARMSTRONG.ALL COPYRIGHT, MANUFACTURING AND	FINISH	MATERIAL	COMMENTS:	SIZE DRG.			REV
-					SALES RIGHTS RESERVED.		MATERIAL SPEC.	DO NOT SCA	LE A1	PX10737		В
REV:	DATE: -	DRN BY: -	CHECKED BY: -	APP. BY: -	THIRD ANGLE PROJECTION		DRAWING RELEASE	DRAWING RELEASE LEVEL:		WEIGHT: KG	SHEET	T 1 OF 1

UNLESS OTHERWISE SPECIFIED: