


UNCONTROLLED



COPPER PIPERWORK 15mm

DIMENSIONS	QUANTITY
A=63	2
B=5	2
C=85	1
D=255	1

NOTES: DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED
 1. COMPLETED SYSTEM TO BE PRESSURE TESTED TO 40 BAR
 2. PIPERWORK TO BE ASSEMBLED USING FITTE TYPE AND PERMANON.

LAST MODIFICATION DETAILS		JOB No.	PART No.	WEIGHT KG	FILE NAME	TITLE		DRG No.	ARMSTRONG HOLDEN BROOKE PULLEN	
DRAWING BORDER CHANGED		-	-	-	13450C	GENERAL ARRANGEMENT PULPRESS PRO STANDARD 1 PUMP - 2.7 BAR SEPARATE GEAR		13450C	MENLOK WAY, MANCHESTER, M12 5UL	
ISSUE DATE/02/2006/DRN PUB		DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.	DATE/08/05/2003/DRN TJM		CHK DUA	APP EGU	TEL: +44 (0) 161 223 2223
CHK PUB APP PUB		-	-	-	-	SCALE NTS		SHEET 1 OF 1		