



NOTE :-  
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY  
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

1 x 230V 50Hz IEC38	POWER WATT	FLC Amps
AUTO MIM.	30	0.25
AUTO MAX.	250	1.30
SPEED 1-4	180-340	1.2-2.10
NPSH (bar)	80°C-0.5	95°C-1.5

LAST MODIFICATION DETAILS

ISSUE	DATE	DRN	APP	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED	JOB No.	PART No.	WEIGHT KG	FILE NAME	TITLE
A	CHK	-	APP		-	-	8.6	-	GENERAL ARRANGEMENT AGE+30-120-1 PUMP

DRG No. AGE301201

DATE 02/03/2011 DRN BSD  
 CHK BSD APP PK  
 SCALE 1:1 SHEET 1 OF 1

**ARMSTRONG**

WENLOCK WAY, MANCHESTER, M12 5JL  
 TEL: +44 (0) 161 223 2223