



FLANGE DUAL DRILLED  
 BS4504 PN6/PN10  
 4-HOLES Ø14 EQUI-SPACED DN A  
 100 PCD  
 4-HOLES Ø19 EQUI-SPACED DN A  
 110 PCD

1 x 230V	POWER	FLC
50Hz IEC38	W/ATT	Amps
AUTD MIM.	30	0.25
AUTD MAX.	350	2.2
SPEED 1-4	190-350	1.2-2.2
NPSH (bar)	80°C-0.5	95°C-1.5

NOTE :-  
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY  
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

LAST MODIFICATION DETAILS

ISSUE	DATE	DRN	APP	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED
A	CHK	APP		

JOB No.	PART No.	WEIGHT KG	FILE NAME	TITLE
-	-	12.8	-	GENERAL ARRANGEMENT
DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.	AGE+40-100-1 PUMP
-	-	-	-	

THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.

DRG No.	AGE 401001
DATE	02/03/2011
CHK	BSD
SCALE	1:1
DRN	BSD
APP	PK
SHEET	1 OF 1

**ARMSTRONG**  
 VENLUDOK WAY, MANCHESTER, M12 5JL  
 TEL: +44 (0) 161 223 2223