



FLANGE DUAL DRILLED
 BS4504 PN6/PN10
 4-HOLES Ø14 EQUI-SPACED DN A
 100 PCD
 4-HOLES Ø19 EQUI-SPACED DN A
 110 PCD

1 x 230V	POWER	FLC
50Hz IEC38	W/ATT	Amps
AUTD MIM.	60	0.9
AUTD MAX.	700	4.0
SPEED 1-4	300-700	2.0-4.0
NPSH (bar)	80°C-0.5	95°C-1.5

NOTE :-
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

LAST MODIFICATION DETAILS

ISSUE	DATE	BY	APP	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED
A	CHK	DRN	APP	

JOB No. - PART No. - WEIGHT KG 16.5 FILE NAME -
 DESIGN No. - PATTERN No. - MATERIAL - MAT'L SPEC. -
 TITLE: GENERAL ARRANGEMENT
 AGE+40-140-1 PUMP
 DRG No. AGE401401
 DATE 02/03/2011 DRN BSD
 CHK BSD APP PK
 SCALE 1:1 SHEET 1 OF 1
ARMSTRONG
 WENLOCK WAY, MANCHESTER, M12 5JL
 TEL: +44 (0) 161 223 2223