



FLANGE DUAL DRILLED  
 BS4504 PN6/PN10  
 4-HOLES Ø14 EQUI-SPACED DN A  
 100 PCD  
 4-HOLES Ø18 EQUI-SPACED DN A  
 110 PCD

NOTE :-  
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY  
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

1 x 230V	POWER	FLC
50Hz IEC38	WATT	Amps
AUTO MIN.	30	0.25
AUTO MAX.	350	2.2
SPEED 1-4	190-350	1.2-2.2
NPSH (bar)	80°C-0.5	95°C-1.5

LAST MODIFICATION DETAILS		JOB No.		PART No.		WEIGHT KG		FILE NAME		TITLE	
ALL DIMENSIONS IN mm		-		-		21.98		-		GENERAL ARRANGEMENT	
DRAWN TO BS308		DESIGN No.		PATTERN No.		MATERIAL		MAT'L SPEC.		AGET+40-100-1 PUMP	
WELDING SYMBOLS TO BS499		-		-		-		-		DRG No. AGET 401001	
SURFACE FINISH SHOWN IN		-		-		-		-		DATE 03/03/2011	
MICROMETERS		-		-		-		-		DRN BSD	
MACHINE WHERE SHOWN ✓		-		-		-		-		APP PK	
TO TOLERANCE ± 0.3MM		-		-		-		-		SCALE 1:1	
UNLESS OTHERWISE STATED		-		-		-		-		SHEET 1 OF 1	
ISSUE DATE		-		-		-		-		VENLOEK WAY, MANCHESTER, M12 5JL	
CHK -		-		-		-		-		TEL: +44 (0) 161 223 2223	
APP -		-		-		-		-		<b>ARMSTRONG</b>	