



FLANGE DUAL DRILLED  
 BS4504 PN6/PN10  
 4-HOLES Ø14 EQUI-SPACED DN A  
 130 PCD  
 4-HOLES Ø18 EQUI-SPACED DN A  
 145 PCD

NOTE :-  
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY  
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

1 X 230V 50Hz IECC38	POWER WATT	FLC Amps
AUTO MIN.	100	0.90
AUTO MAX.	1400	9.50
SPEED 1-4	580-1400	4.0-9.50
NPSH (bar)	80°C-0.5	95°C-1.5

LAST MODIFICATION DETAILS

ISSUE	DATE	DRN	APP	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED
A	CHK -	APP -		

JOB No.	PART No.	WEIGHT KG	FILE NAME
-	-	53	-
DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.
-	-	-	-

TITLE  
 GENERAL ARRANGEMENT  
 AGET+65-120-1 PUMP

DRG No. AGET651201

DATE 04/03/2011 DRN BSD  
 CHK BSD APP PK  
 SCALE 1:1 SHEET 1 OF 1

**ARMSTRONG**

VENLICK WAY, MANCHESTER, M12 5JL  
 TEL: +44 (0) 161 223 2223