



2

PIPE SIZE	FLOW USGPM	METER RANGE MIN & MAX GPM	DIMENSIONS						WEIGHT
			A	B	C	D	E	F	
2"	50	25-100	8.10 (206)	0.31 (8)	0.38 (10)	0.25 (6)	0.31 (8)	N/A	2.0 (0.9)
2½"	100	50-200							
3"	150	75-300							
	200	100-400							
3½"	250	125-500							
	300	150-600							
4"	400	200-800	8.50 (216)	0.38 (10)	0.44 (11)	0.38 (10)	0.38 (10)	N/A	2.5 (1.0)
	450	225-900							
	500	250-1000							
5"	750	375-1500	8.25 (210)	0.38 (10)	0.44 (11)	0.38 (10)	0.38 (10)	0.437	3.0 (1.4)
	1000	500-2000							
6"	1250	625-2500	9.25 (235)	0.50 (13)	0.62 (16)	0.50 (13)	0.50 (13)	0.62 (16)	3.0 (1.4)
	1500	750-3000							
8"	2000	1000-4000	8.25 (210)	0.38 (10)	0.44 (11)	0.38 (10)	0.38 (10)	0.437	3.0 (1.4)
	2500	1250-5000							
	3000	1500-6000							
10"	3500	1750-7000	9.25 (235)	0.50 (13)	0.62 (16)	0.50 (13)	0.50 (13)	0.62 (16)	3.0 (1.4)
	4000	2000-8000							
	4500	2250-9000							
12"	5000	2500-10000	9.25 (235)	0.50 (13)	0.62 (16)	0.50 (13)	0.50 (13)	0.62 (16)	3.0 (1.4)

**NOTE:** Dimensions are in inches (mm)  
Weights are in lbs (kg)

## TORONTO

+1 416 755 2291

## BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

## MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

## SÃO PAULO

+55 11 4781 5500