

HORIZONTAL SPLIT CASE PUMP | SERIES 4600F | DIESEL DRIVEN | 14×10×20F | SUBMITTAL

File No: F46-5681
Date: SEPTEMBER 8, 2025
Supersedes: F46-5681
Date: FEBRUARY 16, 2022

Job: _____ Representative: _____
_____ Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____
Head: _____

ENGINE DESIGN DATA

HP: _____ RPM: _____
Bat. Voltage: _____ Tank size: _____
Other: _____

NOTES

- 1 Std. Discharge flange thickness ANSI 250#.
- 2 Coupling guard not shown.
- 3 All dimensions for engine connections are with reference to engine manufacturer's installation drawings.
- 4 Do not use for construction unless certified.
- 5 Right hand rotation only.

FLANGE RATING

- ☐ ANSI 125# STD¹
☐ ANSI 125# Suction
250# Discharge
☐ ANSI 250#

FIRE PUMP LISTING

- ☐ UL
☐ ULC
☐ FM

ACCESSORIES


- Exhaust system
- Fuel system
- Cooling system (mounted on engine)
- Battery system

CLARKE ENGINE

HORIZONTAL SPLIT CASE DIESEL DRIVEN PUMP - 14×10×20F


ENGINE	DIMENSIONS inches (mm)													WEIGHT
	SUCTION	DISCHARGE	C MAX	HA	HB	HE	HF	HM	T	E	SD	K	Z	lbs (kg)
C13HO-UFAD20,22,28,30,32,38,40,50,52,58,60	14	10	127.73 (3245)	40.00 (1016)	128.00 (3252)	38.00 (966)	59.00 (1499)	78.75 (2000)	8.00 (204)	20.30 (516)	41.50 (1055)	6*	20.70 (526)	3250 (1474)
C18HO-UFAA78	14	10	135.03 (3430)	50.00 (1270)	138.00 (3506)	48.00 (1220)	64.00 (1626)	85.6 (2174)	10.00 (254)	20.30 (516)	41.50 (1055)	6*	22.70 (577)	4100 (1860)
C18HO-UFAC10,18,20,28	14	10	135.03 (3430)	50.00 (1270)	138.00 (3506)	48.00 (1220)	64.00 (1626)	85.6 (2174)	10.00 (254)	20.30 (516)	41.50 (1055)	6*	22.70 (577)	4100 (1860)
C18HO-UFAD10,18,20,28,30,38,40,48,50,58,68,70,78,42	14	10	135.03 (3430)	50.00 (1270)	138.00 (3506)	48.00 (1220)	64.00 (1626)	85.6 (2174)	10.00 (254)	20.30 (516)	41.50 (1055)	6*	22.70 (577)	4100 (1860)
C18HO-UFAD12,22,33	14	10	137.23 (3486)	50.00 (1270)	138.00 (3506)	48.00 (1220)	64.00 (1626)	81.0 (2057)	10.00 (254)	20.30 (516)	41.50 (1055)	6*	22.70 (577)	4100 (1860)
DP6H-UFAA88,70,X8	14	10	123.93 (3148)	36.00 (915)	118.00 (2998)	34.00 (864)	54.00 (1372)	79.85 (2028)	6.00 (153)	20.30 (516)	41.50 (1055)	12**	18.70 (475)	2250 (1020)
DQ6H-UFAA50,60,88,98	14	10	122.23 (3105)	36.00 (915)	118.00 (2998)	34.00 (864)	54.00 (1372)	81.45 (2069)	6.00 (153)	20.30 (516)	41.50 (1055)	12**	18.70 (475)	2500 (1134)
DR8H-UFAA40,56,68,62	14	10	117.63 (2988)	40.00 (1016)	118.00 (2998)	38.00 (966)	54.00 (1372)	78.1 (1984)	8.00 (204)	20.30 (516)	41.50 (1055)	6*	20.70 (526)	2700 (1225)
DSOH-UFAA92,98	14	10	123.93 (3148)	40.00 (1016)	118.00 (2998)	38.00 (966)	54.00 (1372)	81.15 (2061)	8.00 (204)	20.30 (516)	41.50 (1055)	6*	20.70 (526)	3200 (1450)
DSOH-UFAANO,68,60,MO	14	10	126.03 (3202)	40.00 (1016)	118.00 (2998)	38.00 (966)	54.00 (1372)	81.15 (2061)	8.00 (204)	20.30 (516)	41.50 (1055)	6*	20.70 (526)	3200 (1450)
DT2H-UFAA58,50,88	14	10	133.43 (3390)	54.00 (1372)	128.00 (3252)	52.00 (1321)	59.00 (1499)	83.05 (2109)	10.00 (254)	20.30 (516)	41.50 (1055)	6*	22.70 (577)	4500 (2040)
JU6H-UFADQO,RO	14	10	114.33 (2904)	32.00 (813)	98.00 (2490)	30.00 (762)	44.00 (1118)	78.15 (1985)	6.00 (153)	18.70 (475)	41.50 (1055)	12**	18.70 (475)	1747 (791)
JU6H-UFADQO,RO	14	10	109.63 (2785)	32.00 (813)	98.00 (2490)	30.00 (762)	44.00 (1118)	78.15 (1985)	6.00 (153)	18.70 (475)	41.50 (1055)	12**	18.70 (475)	1747 (791)
JW6H-UFAD70,80,FO,JO,DO	14	10	122.03 (3100)	36.00 (915)	118.00 (2998)	34.00 (864)	54.00 (1372)	83.65 (2125)	6.00 (153)	20.30 (516)	41.50 (1055)	12**	18.70 (475)	2094 (948)
C32HO-UFAC10,18,20,28,30,38,40,48,50,58,60,68,22,32,42,52,62	14	10	148.13 (3763)	60.00 (1524)	148.00 (3760)	58.00 (1474)	46.00 (1169)	87.5 (2223)	12.00 (305)	20.30 (516)	41.50 (1055)	8*	24.70 (628)	7200 (3265)

NOTE:
* Bottom Flange only
** Top & Bottom Flanges



CUMMINS ENGINE
HORIZONTAL SPLIT CASE DIESEL DRIVEN PUMP - 14×10×20F

ENGINE	DIMENSIONS inches (mm)							WEIGHT
	C	HA	HB	HE	HF	HM	Z	lbs (kg)
CFP9E series	141.09 (3584)	32.00 (813)	122.00 (3099)	30.00 (762)	39.00 (991)	77.37 (1965)	18.25 (464)	5934 (2692)
CFP15E series	142.77 (3626)	40.00 (1016)	145.00 (3683)	38.00 (965)	47.00 (1194)	74.15 (1883)	18.25 (464)	7314 (3318)



TORONTO

23 BERTRAND AVENUE,
TORONTO, ONTARIO,
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE, NORTH
TONAWANDA, NEW YORK,
U.S.A., 14120-6594
+1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS
BUSINESS PARK, DROITWICH SPA,
WORCESTERSHIRE,
UNITED KINGDOM, WR9 0LW
+44 8444 145 145

MANCHESTER

WOLVERTON STREET, MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#18, LEWIS WORKSPACE, 3RD FLOOR,
OFF MILLERS - NANDIDURGA ROAD,
JAYAMAHAL CBD, BENSON TOWN,
BANGALORE, INDIA 560 046
+91 80 6510 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

BEIJING

ROOM 1612, NANYIN BUILDING NO.2
NORTH EAST THRID RING ROAD
CHAOYANG DISTRICT, BEIJING,
CHINA 100027
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES
AGOSTINHO, 1370 GALPÃO 6 EMBU
DAS ARTES, SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 20 10 26 21

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O.BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

FRANKFURT

WESTERBACHSTRASSE 32,
D-61476 KRONBERG IM TAUNUS
GERMANY
+49 6173 999 77 55

ARMSTRONG FLUID TECHNOLOGY®
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM