

VERTICAL IN-LINE FIRE PUMP 43PF | 8 x 6 x 18 PF | SUBMITTAL

File No: F43.103U
Date: OCTOBER 9, 2025
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____
Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____
Head: _____

ENCLOSURE: _____

FIRE PUMP LISTING

- ☐ UL
☐ ULC
☐ FM


FLANGE RATING

- ☐ ANSI 125# STD
☐ ANSI 250# STD

- Dimensions are not to be used for construction purposes unless certified.
- Data subject to change without notice.

MOTOR DATA

HP: _____ RPM: _____
Volt: _____ ph: _____ Hz: _____



PUMP DATA

PUMP	DIMENSIONS inches (mm)						WEIGHT
MODEL	A	B	C	D	E	X	lbs (kgs)
43PF 8×6×18PF	8.00 (203)	6.00 (152)	27.00 (685)	21.75 (552)	13.38 (339)	17.88 (454)	1143 (518.5)

UL LISTED MOTOR DATA

MOTOR	DIMENSIONS inches (mm)			WEIGHT
FRAME	F MAX	AG MAX	H MAX	lbs (kgs)
326TC	15.95 (405)	41.74 (1060)	11.66 (296)	518 (235.0)
364/365TC	18.50 (469)	46.06 (1169)	16.50 (419)	848 (395.0)
404/405TC	19.50 (495)	51.55 (1309)	16.40 (416)	1102 (500.0)
444/445TC	22.71 (576)	55.97 (1421)	18.54 (470)	1444 (655.0)

TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 6510 3555

SHANGHAI
+86 21 5237 0909

BEIJING
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 20 10 26 21

DUBAI
+971 4 887 6775

JIMBOLIA
+40 256 360 030

FRANKFURT
+49 6173 999 77 55