

# VERTICAL TURBINE DIESEL FIRE PUMP | 2000 GPM WITH 10×20 FABRICATED STEEL HEAD | SUBMITTAL

File No: F51.626

Date: JULY 15, 2013

Supersedes: F51.626

Date: AUGUST 15, 2005

Job:		Representative:					
Engineer:		Order no.:	Date:				
		Submitted by:	Date:				
		Approved by:	Date:				
Model: 10×15H VTF	<b>Discharge head:</b> 10×20 F	NOTES					
<b>RPM:</b> 1770 Water lube <b>2000 GPM:</b>	T.D.H	Dimension based or driver adaptor is req	n randolph gear drive. May vary when uired.				
☐ FM ☐ UL	☐ NFPA-20 only	Dimensions are in in	ches unless otherwise indicated.				
☐ Approval ☐ Constru	ction	<ul> <li>Engine to base mounting and cooling loop to be fie installed and plumbed.</li> </ul>					
☐ Engine model:		Engine oil & anti free	eze/coolant may not be included.				
☐ Ragd model:		• Gear shipped filled v	vith oil. Check level before installation.				
☐ Shaft model:		Refer dwg. no	for Engine dimensions.				
☐ Controller model:		Not to be used for co	onstruction unless certified.				
PRESS DISCHARGE FLAT		— FM	ا				
RATE DA DC	DD DE DG	DK :	rt VI IIIC				

STG'S	DISCHARGE SIZE	RATING	RAGD	AG*	В	С	н*	I*	L	AA
	INCH (mm)		НР	INCH (mm)						
5	10.00 (254)	300	400	36.00 (914)	97.25 (2470)				_	_
5	10.00 (254)	300	500	45.44 (1154)	97.25 (2470)	1.94 (49)	18.75 (476)	28.00 (711)	_	_

**Approved** 

17.50

300 #

15.50

(394)

14.00

(356)

10.00


(254)

1.13

1.88

(49)

<sup>\*</sup> Dimension based on randolph gear drive. May vary when driver adaptor is required.



## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM