


## 2000 gpm with 10 x 20 Fabricated Steel Head

## SUBMITTAL

VERTICAL TURBINE ELECTRIC  
 FIRE PUMP



2000 G.P.M. T.D.H.

- FM  UL  NFPA-20 ONLY  
 APPROVAL  CONSTRUCTION

MODEL 10x15H VTF

10 x 20 "F" DISCHARGE HEAD  
 1770 R.P.M. WATER LUBE

MOTOR \_\_\_\_\_ HP \_\_\_\_\_  
 VOLT \_\_\_\_\_ PH \_\_\_\_\_ HZ \_\_\_\_\_  
 CONTROLLER MODEL \_\_\_\_\_


JOB NAME. \_\_\_\_\_  
 ITEM NO. \_\_\_\_\_

CUSTOMER \_\_\_\_\_

ORDER NO. \_\_\_\_\_  
 MFG. REP. \_\_\_\_\_

DWG. NO. \_\_\_\_\_  
 SERIAL NO. \_\_\_\_\_

NOT TO BE USED FOR CONSTRUCTION UNLESS CERTIFIED  
 By: \_\_\_\_\_ Date: \_\_\_\_\_



- NOTES:
- 1 DIMENSION BASED ON MOTOR HEIGHT OF A STANDARD WP-I HOLLOW SHAFT MOTOR. SUBJECT TO CHANGE DEPENDING ON MOTOR MFG. AND/OR THE USE OF A MOTOR ADAPTOR.
  - 2 DIMENSIONS ARE IN INCHES UNLESS OTHERWISE INDICATED.
  - 3 WHEN MOTOR IS OIL LUBRICATED, OIL IS NOT FURNISHED. SEE OPERATION MANUAL FOR MANUFACTURER'S RECOMMENDATIONS.