


3500 gpm with 12 x 24 1/2 Fabricated Steel Head

SUBMITTAL

VERTICAL TURBINE ELECTRIC
 FIRE PUMP



3500 G.P.M. FM UL APPROVAL
 T.D.H. NFPA-20 ONLY CONSTRUCTION

MODEL 12x18M VTF
 12 x 24 1/2 "F" DISCHARGE HEAD
 1770 R.P.M. WATER LUBE

MOTOR _____ HP _____
 VOLT _____ PH _____ HZ _____
 CONTROLLER MODEL _____


JOB NAME: _____
 ITEM NO. _____

CUSTOMER _____

ORDER NO. _____
 MFG. REP. _____

DWG. NO. _____
 SERIAL NO. _____

By: _____ Date: _____
NOT TO BE USED FOR CONSTRUCTION UNLESS CERTIFIED



NOTES:

1. DIMENSION BASED ON MOTOR HEIGHT OF A STANDARD WP-1 HOLLOW SHAFT MOTOR. SUBJECT TO CHANGE DEPENDING ON MOTOR MFG. AND/OR THE USE OF A MOTOR ADAPTOR.
2. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE INDICATED.
3. WHEN MOTOR IS OIL LUBRICATED, OIL IS NOT FURNISHED. SEE OPERATION MANUAL FOR MANUFACTURER'S RECOMMENDATIONS.