




KW RATING	MAX. FUSE SIZE AT 380-500V	50% INDBE RATING	100% RATING	WEIGHT Kgs.
160	400A	73 dBA	74 dBA	151
200	500A	73 dBA	74 dBA	150
250	600A	73 dBA	74 dBA	151



LAST MODIFICATION DETAILS

SEE ECD 8785 (AHBP)
TITLE WAS FC102

ALL DIMENSIONS IN mm
DRAWN TO BS308
WELDING SYMBOLS TO BS499
SURFACE FINISH SHOWN IN MICROMETERS
MACHINE WHERE SHOWN TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED

JOB No.	PART No.	WEIGHT KG	FILE NAME
-	-	-	-

TITLE
IVS102 FREQUENCY INVERTER DRIVE
D2 CHASSIS

DATE	DRN BSD
28/05/2009	APP PK

DRG No. CP12072-B
SCALE 1:1 SHEET 1 OF 1
VENLICK WAY, MANCHESTER, M12 5JL
TEL: +44 (0) 161 223 2223

