




**EXTENDED SPEED**



Performance curves are for reference only.  
Confirm current performance data with Armstrong ACE Online selection software.

**DIMENSION DATA**

**INDOOR**  
(UL TYPE 12/ODP)

- Frame size: 145JM
- Size: 1.5×1×8
- HP: 2
- RPM: 1800
- A: 5.50 (140)
- B: 5.91 (150)
- C MAX: 19.70 (500)
- D1: 5.25 (133)
- D2: 3.50 (89)
- 2E: 7.09 (180)
- F: 5.00 (127)
- H: 0.40 (10)
- HD: 5.71 (145)
- HI: 22.33 (567)
- HV: 12.28 (312)
- N: 5.79 (147)
- NAN1: 6.00 (152)
- X: 6.50 (165)
- Y: 4.00 (102)
- Casing foot hole: 0.63 (16)
- Weight: 245 (111.1)

Dimensions - inch (mm)  
Weight - lbs (kg)

**INDOOR**

- TORONTO  
+1 416 755 2291
- BUFFALO  
+1 716 693 8813
- BIRMINGHAM  
+44 (0) 8444 145 145
- MANCHESTER  
+44 (0) 8444 145 145
- BANGALORE  
+91 (0) 80 4906 3555
- SHANGHAI  
+86 21 3756 6696
- SÃO PAULO  
+55 11 4781 5500

