


EXTENDED SPEED



Performance curves are for reference only.
Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

INDOOR
(UL TYPE 12/ODP)

- Frame size: 145JM
- Size: 3×1.5×8
- HP: 2
- RPM: 1800
- A: 5.50 (140)
- B: 5.91 (150)
- C MAX: 19.71 (501)
- D1: 5.63 (143)
- D2: 3.50 (89)
- 2E: 7.09 (180)
- F: 5.00 (127)
- H: 0.40 (10)
- HD: 5.71 (145)
- HI: 22.34 (567)
- HV: 12.28 (312)
- N: 5.80 (147)
- NAN1: 6.00 (152)
- X: 8.50 (216)
- Y: 4.00 (102)
- Casing foot hole: 0.63 (16)
- Weight: 265 (120.2)

Dimensions - inch (mm)
Weight - lbs (kg)

INDOOR

- TORONTO
+1 416 755 2291
- BUFFALO
+1 716 693 8813
- BIRMINGHAM
+44 (0) 8444 145 145
- MANCHESTER
+44 (0) 8444 145 145
- BANGALORE
+91 (0) 80 4906 3555
- SHANGHAI
+86 21 3756 6696
- SÃO PAULO
+55 11 4781 5500

