



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		(N1) INLET	4" FLG (102)	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	(N2) OUTLET	4" FLG (102)	
THWX-1436-4-4	51 -3/8	1305	35-3/4	908	38	965	24-1/2	622	(N3) DRAIN	1/2" NPT (13)	
THWX-1442-4-4	57 -3/8	1457	41-3/4	1060	44	1118	30-1/2	775	COLLAR ASSEMBLY		
THWX-1448-4-4	63 -3/8	1610	47-3/4	1213	50	1270	36-1/2	927	STANDARD OVS. FOR STONE LINING		
THWX-1454-4-4	69 -3/8	1762	53-3/4	1365	56	1422	42-1/2	1080	"E"	14" (356)	16" (406)
THWX-1460-4-4	75 -3/8	1915	59-3/4	1518	62	1575	48-1/2	1232	"F"	10-1/2" (267)	12" (305)
THWX-1466-4-4	81 -3/8	2067	65-3/4	1670	68	1727	54-1/2	1384	DESIGN CONDITIONS		
THWX-1472-4-4	87 -3/8	2219	71-3/4	1822	74	1880	60-1/2	1537	TUBES		
THWX-1478-4-4	93 -3/8	2372	77-3/4	1975	80	2032	66-1/2	1689	DESIGN PRESSURE	150 PSIG	1034 KPa
THWX-1484-4-4	99 -3/8	2524	83-3/4	2127	86	2184	72-1/2	1842	DESIGN TEMPERATURE	375 F	191 C
THWX-1490-4-4	105 -3/8	2677	89-3/4	2280	92	2337	78-1/2	1994	M.D.M.T.	40 F	4.4 C
THWX-1496-4-4	111 -3/8	2829	95-3/4	2432	98	2489	84-1/2	2146	HYD. TEST PRESSURE	225 PSIG	1551 KPa
THWX-14102-4-4	117 -3/8	2981	101-3/4	2584	104	2642	90-1/2	2299	NOTES:		
THWX-14108-4-4	123 -3/8	3134	107-3/4	2737	110	2794	96-1/2	2451	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THWX-14114-4-4	129 -3/8	3286	113-3/4	2889	116	2946	102-1/2	2604	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THWX-14120-4-4	135 -3/8	3439	119-3/4	3042	122	3099	108-1/2	2756	3. DRAWING IS NOT TO SCALE.		
THWX-14126-4-4	141 -3/8	3591	125-3/4	3194	128	3251	114-1/2	2908	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THWX-14132-4-4	147 -3/8	3743	131-3/4	3346	134	3404	120-1/2	3061	5. DIMENSIONS SHOWN AS: In.(mm)		
THWX-14138-4-4	153 -3/8	3896	137-3/4	3499	140	3556	126-1/2	3213	CUSTOMER:		
THWX-14144-4-4	159 -3/8	4048	143-3/4	3651	146	3708	132-1/2	3366	LOCATION:		
THWX-14150-4-4	165 -3/8	4201	149-3/4	3804	152	3861	138-1/2	3518	ENGINEER :		
THWX-14156-4-4	171 -3/8	4353	155-3/4	3956	158	4013	144-1/2	3670	ORDER No.:		
THWX-14162-4-4	177 -3/8	4505	161-3/4	4108	164	4166	150-1/2	3823	PROJECT/JOB:		
									LOCATION:		
									TAG:		
									QUOTE #		

TITLE G.A. 150 LB. TANK HEATERS

ARMSTRONG

NUMBER

REV.

DATE : 24/05/95

BY : D.C.R

TORONTO - CANADA
TEL : (416) 755-2291

MONTREAL - CANADA
TEL : (514) 421-2424

BUFFALO - N. Y.
TEL : (716) 693-8813

COLCHESTER - U.K.
TEL : (44) 120-657-9491

Thwx-14-4P-4