



Vertical In-Line Pump

Design Envelope,
IVS & Conventional

Parts list

File No: 6012.100
Date: FEBRUARY 09, 2024
Supersedes: 6012.100
Date: JANUARY 20, 2023

—

—

—

—

CONTENTS

INTRODUCTION	4
4300, 4302 & 4312 PARTS LIST	5
4380, 4382 & 4392 PARTS LIST	6
4300/4302/4312/4380/4382/4392 CASING GASKET	7
COUPLING KIT	8
4300, 4302 & 4312 MECHANICAL SEAL KIT - OUTSIDE	11
4300, 4302 & 4312 MECHANICAL SEAL - INSIDE	11
4300 REPLACEMENT SEAL - OUTSIDE	12
4300 REPLACEMENT SEAL KIT - OUTSIDE	18
4300 REPLACEMENT SEAL - INSIDE	21
4302 REPLACEMENT SEAL - OUTSIDE	23
4302 REPLACEMENT SEAL KIT - OUTSIDE	24
4302 REPLACEMENT SEAL - INSIDE	25
4312 REPLACEMENT SEAL - OUTSIDE	27
4312 REPLACEMENT SEAL KIT - OUTSIDE	28
4312 REPLACEMENT SEAL - INSIDE	28
4380, 4382 & 4392 MECHANICAL SEAL KIT - INSIDE	29
4380, 4382 & 4392 REPLACEMENT SEAL KIT - INSIDE	29
4380 REPLACEMENT SEAL	30
4380 REPLACEMENT SEAL KIT - INSIDE	31
4382 REPLACEMENT SEAL KIT - INSIDE	34
4392 REPLACEMENT SEAL KIT - INSIDE	36
STANDARD FLUSH LINE REPLACEMENT PARTS AND KITS	37

NOTE: USE CONFIGURATOR FOR CASING, IMPELLER, MOTOR AND VARIABLE FREQUENCY DRIVE (VFD)

Introduction

Armstrong was founded on the core values of Community, Service, Learning and Innovation. Reflecting our commitment to service, Armstrong now provides 360 Service and Support. Working collaboratively with the 'partner' companies in our network, we're ready to provide the service and support that customers need in relation to building performance.

A key part of serving our customers is providing Genuine Armstrong Replacement Parts to support installations of our products. But the value we provide goes beyond the quality of the replacement part.

With the availability of parts in packaged kits, you'll never have to leave a repair incomplete just because you didn't have all the pieces required for the job. And you won't have to pay a premium for rush delivery of additional parts.

Your customers will be happier, because their mechanical systems will be returned to service earlier. That means you'll be more likely to get their repeat business.

The Armstrong replacement parts program serves contractors and end customers through a combination of: Availability, Easy Selection, Easy Transactions, Quick Delivery and Technical Support.

AVAILABILITY

- Dedicated service parts inventory
- Real-time inventory information
- Active channel inventory management

EASY SELECTION

- Parts selection charts with updated descriptions, pictures and sizing details
- Illustrated part selection information
- Product details on packaging
- All items within each Parts Kit are carefully selected for accurate sizing

EASE OF TRANSACTION

- Parts and Kits available in [ADEPT](#) Locator tool for local parts dealers
- Complete parts kits reduce the work to source items.
- One search and one order address a service issue


QUICK DELIVERY OF PARTS SOLUTIONS

- On-time shipment
- Options for shipping service levels
- Parts Kits include all parts and related items required to complete replacement work

SUPPORT


- Trained Armstrong support professionals
- Dedicated 24x7 service and support parts

4300, 4302 & 4312 PARTS LIST




ITEM	DESCRIPTION
①	Casing Gasket
⑧	Coupling
⑦	Cover Seal
⑨	Flush Line
③	Impeller
④	Impeller Cap Screw
⑤	Impeller Washer
⑥	Mechanical Seal
②	Shaft

4380, 4382 & 4392 PARTS LIST



ITEM	DESCRIPTION
①	Casing Gasket
③	Impeller
④	Impeller Cap Screw
⑤	Impeller Washer
⑥	Mechanical Seal

4300/4302/4312/4380/4382/4392 CASING GASKET




ITEM	DESCRIPTION
①	Casing Gasket

PUMP SIZE	PART NUMBER	QTY REQUIRED
1.5x1.5x6	8426401-002	1
2x2x6	8426401-002	1
3x3x6	8426401-002	1
4x4x6	8426401-002	1
6x6x6	8426401-002	1
2.5x2.5x7.5	8426401-003	1
3x3x7.5	8426401-003	1
5x5x7.5	8426401-003	1
1.5x1.5x8	8426401-003	1
2x2x8	8426401-003	1
3x3x8	8426401-003	1
4x4x8	8426401-003	1
5x5x8	8426401-003	1
6x6x8	8426401-003	1
8x8x8	8426401-003	1
1.5x1.5x10	8426401-004	1
2x2x10	8426401-004	1
3x3x10	8426401-004	1
4x4x10	8426401-004	1
6x6x10	8426401-004	1
8x8x10	8426401-004	1

PUMP SIZE	PART NUMBER	QTY REQUIRED
4x4x11.5	8426401-006	1
5x5x11.5	8426401-006	1
6x6x11.5	8426401-006	1
8x8x11.5	8426401-006	1
3x3x13	8426401-005	1
4x4x13	8426401-005	1
5x5x13	8426401-005	1
5x5x13H	8426401-005	1
6x6x13	8426401-005	1
6x6x13H	8426401-005	1
8x8x13	8426401-005	1
10x10x13	8426401-005	1
8x8x15	8426401-008	1
8x8x15L	8426401-008	1
10x10x15	8426401-008	1
3x3x6B*	8426401-002	1
4x4x6C*	8426401-002	1
5x5x6*	8426401-002	1

* 4300/4380 Medium Pump Casing Gasket

COUPLING KIT



ITEM	DESCRIPTION
13	Capscrew
14	Motor Collar
15	Motor Shaft Setscrew
16	Pump Collar
20	Pump Collar Washer
17	Pump Shaft end Capscrew
18	Split Coupling
19	Washer

PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED
1.5x1.5x6	143TC 145TC	8427731-000K	1
2x2x6			
3x3x6			
4x4x6			
6x6x6			
1.5x1.5x8			
2x2x8			
3x3x8			
4x4x8			
5x5x8			
1.5x1.5x10			
2x2x10			
3x3x10			
1.5x1.5x6	182TC 184TC	8427732-000K	1
2x2x6			
3x3x6			
4x4x6			
6x6x6			
1.5x1.5x8			
2x2x8			
3x3x8			
4x4x8			

PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED
5x5x8	182TC 184TC	8427732-000K	1
6x6x8			
8x8x8			
1.5x1.5x10			
2x2x10			
3x3x10			
4x4x10			
6x6x10			
8x8x10			
4x4x11.5			
5x5x11.5			
6x6x11.5			
2x2x6			
3x3x6			
4x4x6			
6x6x6			
1.5x1.5x8			
2x2x8			
3x3x8			
4x4x8			
5x5x8			
6x6x8			

PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED	PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED
8x8x8	213TC 215TC	8427733-000K	1	8x8x10	284TC 286TC	8427736-000K	1
1.5x1.5x10				4x4x11.5			
2x2x10				5x5x11.5			
3x3x10				6x6x11.5			
4x4x10				8x8x11.5			
6x6x10				3x3x13			
8x8x10				4x4x13			
4x4x11.5				5x5x13			
5x5x11.5				5x5x13H			
6x6x11.5				6x6x13			
3x3x6	254TC 256TC	8427734-000K	1	6x6x13H	324TSC 326TSC	8427737-000K	1
4x4x6				8x8x13			
1.5x1.5x8				10x10x13			
2x2x8				3x3x8			
3x3x8				4x4x8			
4x4x8				5x5x8			
5x5x8				1.5x1.5x10			
6x6x8				2x2x10			
8x8x8				3x3x10			
1.5x1.5x10				4x4x10			
2x2x10	6x6x10						
3x3x10	3x3x13						
4x4x10	324TC 326TC	8427738-000K	1	8x8x10	364TC 365TC	8427739-000K	1
6x6x10				4x4x11.5			
8x8x10				5x5x11.5			
4x4x11.5				6x6x11.5			
5x5x11.5				8x8x11.5			
6x6x11.5				4x4x13			
8x8x11.5				5x5x13			
2x2x8				5x5x13H			
3x3x8				6x6x13			
4x4x8				6x6x13H			
5x5x8	8x8x13						
1.5x1.5x10	10x10x13						
2x2x10	8x8x11.5						
3x3x10	5x5x13						
4x4x10	5x5x13H						
6x6x10	6x6x13						
	8x8x13						

Vertical In-line
Pump


PARTS LIST

10

PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED
4x4x8	404TSC 405TSC	8427740-000K	1
6x6x10			
3x3x13			
6x6x10	444TSC 445TSC	8427879-100K	1
3x3x13	182TC 184TC	8427864-000K	1
4x4x13			
3x3x13	213TC 215TC	8427865-000K	1
4x4x13			
5x5x13			
6x6x13			
6x6x13H			
8x8x13			
3x3x13	254TC 256TC	8427866-000K	1
4x4x13			
5x5x13			
5x5x13H			
6x6x13			
6x6x13H			
8x8x13			
12x12x13			
12x12x13	284TC 286TC	8427895-000K	1
10x10x15	324TC 326TC	8427867-000K	1
8x8x15			
8x8x15L			
12x12x13			
10x10x13	364TC 365TC	8427868-000K	1
10x10x15			
8x8x15			
8x8x15L			
12x12x13	404TC 405TC	8427869-000K	1
8x8x13			
10x10x13			
6x6x13H			
8x8x13			
10x10x13	404TC 405TC	8427869-000K	1
10x10x15			
8x8x15			
8x8x15L			
12x12x13			

PUMP SIZE	MOTOR FRAME	PART NUMBER	QTY REQUIRED			
8x8x13	444TC 445TC 447TC 449TC	8427870-000K	1			
10x10x13						
10x10x15						
8x8x15						
8x8x15L						
12x12x13	444TSC	8427548-000K	1			
8x8x13						
10x10x13	444TSC 445TSC 447TSC 449TSC	8427879-000K	1			
3x3x13						
2.5x2.5x7.5				254TC 256TC	8427734-000K	1 1
				284TSC 286TSC	8427735-000K	1 1
3x3x7.5	254TC 256TC	8427734-000K	1 1			
	284TSC 286TSC	8427735-000K	1 1			
	324TSC 326TSC	8427737-000K	1 1			
5x5x7.5	286TSC	8427735-000K	1			
	324TSC 326TSC	8427737-000K	1 1			
	364TSC		1			
	364TSC		1			
	365TSC		1			
	405TSC	8427740-000K	1			

4300, 4302 & 4312 MECHANICAL SEAL KIT - OUTSIDE




KIT CONTENTS

ITEM	DESCRIPTION
(21)	Mechanical Seal
(22)	Seal Cover
(23)	Seal Cover Capscrew
(24)	Seal Cover Capscrew Washer

Manu Code	C-SSC AB2	C-SSC G30	SSC-SSC AT70	AC-SSC AT70
Seal type	AB2	G30	AT70	AT70
Rotating Face	Resin Bonded Carbon	Carbon	Sintered Silicon Carbide	Antimony-loaded Carbon
Stationary Seat	Sintered Silicon Carbide	Silicon Carbide	Sintered Silicon Carbide	Sintered Silicon Carbide
Secondary Seal	Viton	Viton	Aflas	Aflas
Legend (Refer App.Guide)	A1-2	G30	A3	A4

4300, 4302 & 4312 MECHANICAL SEAL - INSIDE



KIT CONTENTS

ITEM	DESCRIPTION
(28)	Mechanical Seal


Manu Code	C-CER 1A
Seal type	Armstrong Type 1A
Rotating Face	Carbon
Stationary Seat	Ceramic
Secondary Seal	EPDM
Legend (Refer App.Guide)	A2

* Default selection

4300 REPLACEMENT SEAL - OUTSIDE

REPLACEMENT SEAL PART NUMBERS

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
1.5x1.5x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
1.5x1.5x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
10x10x13	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
10x10x15	324-326	8975002-374	8975000-964	8975002-478	8975002-475
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
12x12x13	284-286	8975002-374	8975000-964	8975002-478	8975002-475
	324-326	8975002-374	8975000-964	8975002-478	8975002-475
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
12x12x17	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495
14x14x14	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495
14x14x15	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495
16x16x15	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495
16x16x15H	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495



PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
16x16x15L	364-365	8975002-394	8975000-978	8975002-498	8975002-495
	404-405	8975002-394	8975000-978	8975002-498	8975002-495
	444-449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-394	8975000-978	8975002-498	8975002-495
16x16x19	444	8975002-394	8975000-978	8975002-498	8975002-495
	445	8975002-394	8975000-978	8975002-498	8975002-495
	447	8975002-394	8975000-978	8975002-498	8975002-495
	449	8975002-394	8975000-978	8975002-498	8975002-495
	5000	8975002-468	Consult Factory	Consult Factory	Consult Factory
2x2x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
2x2x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-304	8975000-962	8975002-408	8975002-405
2x2x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
3x3x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
	444-445	8975002-334	8975000-963	8975002-438	8975002-435
	447-449	8975002-334	8975000-963	8975002-438	8975002-435
3x3x13	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
	444-445	8975002-334	8975000-963	8975002-438	8975002-435
	447-449	8975002-334	8975000-963	8975002-438	8975002-435

PARTS LIST

Vertical In-line
Pump

14

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
3x3x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-304	8975000-962	8975002-408	8975002-405
3x3x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
4x4x10	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
444-445	8975002-334	8975000-963	8975002-438	8975002-435	
4x4x11.5	447-449	8975002-334	8975000-963	8975002-438	8975002-435
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
4x4x13	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
404-405	8975002-334	8975000-963	8975002-438	8975002-435	
4x4x13L	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
4x4x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-304	8975000-962	8975002-408	8975002-405

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
4x4x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-405	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
5x5x11.5	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
5x5x13	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
5x5x13H	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
5x5x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
6x6x10	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
	444-445	8975002-334	8975000-963	8975002-438	8975002-435
	447-449	8975002-334	8975000-963	8975002-438	8975002-435
6x6x11.5	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
6x6x13	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
6x6x13H	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
6x6x13L	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
6x6x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
6x6x8	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
8x8x10	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
8x8x11.5	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
8x8x13	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
447-449	8975002-374	8975000-964	8975002-478	8975002-475	
8x8x13L	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
447-449	8975002-374	8975000-964	8975002-478	8975002-475	

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
8x8x15	284-286	8975002-374	8975000-964	8975002-478	8975002-475
	324-326	8975002-374	8975000-964	8975002-478	8975002-475
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
8x8x15L	284-286	8975002-374	8975000-964	8975002-478	8975002-475
	324-326	8975002-374	8975000-964	8975002-478	8975002-475
	364-365	8975002-374	8975000-964	8975002-478	8975002-475
	404-405	8975002-374	8975000-964	8975002-478	8975002-475
	444-445	8975002-374	8975000-964	8975002-478	8975002-475
	447-449	8975002-374	8975000-964	8975002-478	8975002-475
8x8x8	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
3x3x6B	143TC-145TC	8975002-304	8975000-962	8975002-408	8975002-405
	213TC-215TC	8975002-304	8975000-962	8975002-408	8975002-405
	254TC-256TC	8975002-304	8975000-962	8975002-408	8975002-405
	284TSC-286TSC	8975002-334	8975000-963	8975002-438	8975002-435
4x4x6C	143TC-145TC	8975002-304	8975000-962	8975002-408	8975002-405
	182TC-184TC	8975002-304	8975000-962	8975002-408	8975002-405
	254TC-256TC	8975002-304	8975000-962	8975002-408	8975002-405
	284TSC-286TSC	8975002-334	8975000-963	8975002-438	8975002-435
	324TSC -326TSC	8975002-334	8975000-963	8975002-438	8975002-435
5x5x6	182TC-184TC	8975002-304	8975000-962	8975002-408	8975002-405
	213TC	8975002-304	8975000-962	8975002-408	8975002-405
	256TC	8975002-304	8975000-962	8975002-408	8975002-405
	284TSC-286TSC	8975002-334	8975000-963	8975002-438	8975002-435
	324TSC -326TSC	8975002-334	8975000-963	8975002-438	8975002-435
2.5x2.5x7.5	254TC	8975002-304	8975000-962	8975002-408	8975002-405
	256TC	8975002-304	8975000-962	8975002-408	8975002-405
	284TSC	8975002-334	8975000-963	8975002-438	8975002-435
	286TSC	8975002-334	8975000-963	8975002-438	8975002-435
3x3x7.5	254TC	8975002-304	8975000-962	8975002-408	8975002-405
	256TC	8975002-304	8975000-962	8975002-408	8975002-405
	284TSC	8975002-334	8975000-963	8975002-438	8975002-435
	286TSC	8975002-334	8975000-963	8975002-438	8975002-435
	324TSC	8975002-334	8975000-963	8975002-438	8975002-435
	326TSC	8975002-334	8975000-963	8975002-438	8975002-435
5x5x7.5	286TSC	8975002-334	8975000-963	8975002-438	8975002-435
	324TSC	8975002-334	8975000-963	8975002-438	8975002-435
	326TSC	8975002-334	8975000-963	8975002-438	8975002-435
	364TSC	8975002-334	8975000-963	8975002-438	8975002-435
	364TSC	8975002-334	8975000-963	8975002-438	8975002-435
	365TSC	8975002-334	8975000-963	8975002-438	8975002-435
	405TSC	8975002-334	8975000-963	8975002-438	8975002-435

4300 REPLACEMENT SEAL KIT - OUTSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
1.5x1.5x6	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
1.5x1.5x8	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
10x10x13	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-374K	—	—	—
10x10x15	404-405	8975002-374K	—	—	—
	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
	5000	8975002-394K	—	—	—
12x12x13	284-286	8975002-374K	—	—	—
	324-326	8975002-374K	—	—	—
	364-365	8975002-374K	—	—	—
	404-405	8975002-374K	—	—	—
	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
12x12x17	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
14x14x14	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
14x14x15	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
16x16x15	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
16x16x15H	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
16x16x15L	364-365	8975002-394K	—	—	—
	404-405	8975002-394K	—	—	—
	444-449	8975002-394K	—	—	—
	5000	8975002-394K	—	—	—
16x16x19	444-444	8975002-394K	—	—	—
	445-445	8975002-394K	—	—	—
	447-447	8975002-394K	—	—	—
	449-449	8975002-394K	—	—	—
2x2x10	5000	—	—	—	—
	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
2x2x6	364-365	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—
	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
2x2x8	254-256	8975002-304K	—	—	—
	284-286	8975002-304K	—	—	—
	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
3x3x10	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—
	444-445	8975002-334K	—	—	—
	447-449	8975002-334K	—	—	—
3x3x13	182-184	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—
444-445	8975002-334K	—	—	—	
447-449	8975002-334K	—	—	—	

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
3x3x6	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-304K	—	—	—
3x3x8	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
4x4x10	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—
	444-445	8975002-334K	—	—	—
	447-449	8975002-334K	—	—	—
4x4x11.5	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
4x4x13	182-184	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
4x4x13L	182-184	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
4x4x6	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-304K	—	—	—

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
4x4x8	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
5x5x11.5	364-405	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
5x5x13	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	182-184	8975002-334K	—	—	—
5x5x13H	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
5x5x8	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
6x6x10	364-365	8975002-334K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
6x6x11.5	404-405	8975002-334K	—	—	—
	444-445	8975002-334K	—	—	—
	447-449	8975002-334K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
6x6x13	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—

PARTS LIST

Vertical In-line
Pump

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
6x6x13H	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-374K	—	—	—
	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
6x6x13L	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
6x6x6	143-145	8975002-304K	—	—	—
	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
6x6x8	182-184	8975002-304K	—	—	—
	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
8x8x10	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
8x8x11.5	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-334K	—	—	—

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
8x8x13	182-184	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-334K	—	—	—
	404-405	8975002-374K	—	—	—
	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
8x8x13L	182-184	8975002-334K	—	—	—
	213-215	8975002-334K	—	—	—
	254-256	8975002-334K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—
	364-365	8975002-374K	—	—	—
	404-405	8975002-374K	—	—	—
8x8x15	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
	284-286	8975002-374K	—	—	—
	324-326	8975002-374K	—	—	—
	364-365	8975002-374K	—	—	—
	404-405	8975002-374K	—	—	—
8x8x15L	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
	284-286	8975002-374K	—	—	—
	324-326	8975002-374K	—	—	—
	364-365	8975002-374K	—	—	—
8x8x8	404-405	8975002-374K	—	—	—
	444-445	8975002-374K	—	—	—
	447-449	8975002-374K	—	—	—
	182-184	8975002-304K	—	—	—
8x8x8	213-215	8975002-304K	—	—	—
	254-256	8975002-304K	—	—	—
	284-286	8975002-334K	—	—	—
	324-326	8975002-334K	—	—	—

4300 REPLACEMENT SEAL - INSIDE

REPLACEMENT SEAL PART NUMBERS

PUMP SIZE	FRAME	PART NUMBER	PUMP SIZE	FRAME	PART NUMBER	PUMP SIZE	FRAME	PART NUMBER			
		A2			A2			A2			
1.5x1.5x6	143-145	8975001-507	16x16x19	444-444	Consult factory	3x3x8	143-145	8975001-507			
	182-184	8975001-507		445-445	Consult factory		182-184	8975001-507			
	213-215	8975001-507		447-447	Consult factory		213-215	8975001-507			
1.5x1.5x8	143-145	8975001-507		449-449	Consult factory		254-256	8975001-507			
	182-184	8975001-507		5000	Consult factory		284-286	8975001-537			
	213-215	8975001-507	2x2x10	143-145	8975001-507	324-326	8975001-537				
254-256	8975001-507	182-184		8975001-507	364-365	8975001-537					
10x10x13	284-286	8975001-537		213-215	8975001-507	4x4x10	143-145	8975001-507			
	324-326	8975001-537		254-256	8975001-507		182-184	8975001-507			
	364-365	8975001-577		284-286	8975001-537		213-215	8975001-507			
	404-405	8975001-577	324-326	8975001-537	254-256		8975001-507				
	444-445	8975001-577	364-365	8975001-537	284-286		8975001-537				
447-449	8975001-577	404-405	8975001-537	324-326	8975001-537	4x4x11.5	182-184	8975001-507			
10x10x15	324-326	8975001-577	2x2x6	143-145	8975001-507		213-215	8975001-507			
	364-365	8975001-577		182-184	8975001-507		254-256	8975001-507			
	404-405	8975001-577		213-215	8975001-507		284-286	8975001-537			
	444-445	8975001-577		254-256	8975001-507		324-326	8975001-537			
447-449	8975001-577	284-286	8975001-507	2x2x8	143-145	8975001-507	4x4x13	182-184	8975001-507		
12x12x13	284-286	8975001-577	3x3x10		143-145	8975001-507		213-215	8975001-507	213-215	8975001-507
	324-326	8975001-577			182-184	8975001-507		254-256	8975001-507	254-256	8975001-537
	364-365	8975001-577			213-215	8975001-507		284-286	8975001-537	284-286	8975001-537
	404-405	8975001-577			254-256	8975001-507		324-326	8975001-537	324-326	8975001-537
	444-445	8975001-577		284-286	8975001-507	364-365	8975001-537	364-365	8975001-537		
447-449	8975001-577	324-326	8975001-537	404-405	8975001-537	404-405	8975001-537	4x4x13L	182-184	8975001-537	
12x12x17	364-365	Consult factory	3x3x13	143-145	8975001-507	213-215	8975001-507		254-256	8975001-537	
	404-405	Consult factory		182-184	8975001-507	254-256	8975001-507		284-286	8975001-537	
	444-449	Consult factory		213-215	8975001-507	284-286	8975001-537		324-326	8975001-537	
	5000	Consult factory		254-256	8975001-507	324-326	8975001-537		364-365	8975001-537	
14x14x14	364-365	Consult factory	3x3x6	143-145	8975001-507	4x4x6	143-145	8975001-507			
	404-405	Consult factory		182-184	8975001-507		182-184	8975001-507			
	444-449	Consult factory		213-215	8975001-507		213-215	8975001-507			
	5000	Consult factory		254-256	8975001-507		254-256	8975001-507			
14x14x15	364-365	Consult factory	3x3x6	284-286	8975001-537	4x4x8	284-286	8975001-507			
	404-405	Consult factory		324-326	8975001-537		143-145	8975001-507			
	444-449	Consult factory		364-365	8975001-537		182-184	8975001-507			
	5000	Consult factory		404-405	8975001-537		213-215	8975001-507			
16x16x15	364-365	Consult factory	3x3x6	444-445	8975001-537	4x4x8	254-256	8975001-507			
	404-405	Consult factory		447-449	8975001-537		284-286	8975001-537			
	444-449	Consult factory		143-145	8975001-507		324-326	8975001-537			
	5000	Consult factory		182-184	8975001-507		364-405	8975001-537			
16x16x15H	364-365	Consult factory	3x3x6	213-215	8975001-507	4x4x8	404-405	8975001-537			
	404-405	Consult factory		254-256	8975001-507		143-145	8975001-507			
	444-449	Consult factory		284-286	8975001-537		182-184	8975001-507			
	5000	Consult factory		324-326	8975001-537		213-215	8975001-507			
16x16x15L	364-365	Consult factory	3x3x6	364-365	8975001-537	4x4x8	254-256	8975001-507			
	404-405	Consult factory		404-405	8975001-537		284-286	8975001-537			
	444-449	Consult factory		444-445	8975001-537		324-326	8975001-537			
	5000	Consult factory		447-449	8975001-537		364-405	8975001-537			
16x16x15L	364-365	Consult factory	3x3x6	284-286	8975001-507	4x4x8	404-405	8975001-537			
	404-405	Consult factory		143-145	8975001-507		143-145	8975001-507			
	444-449	Consult factory		182-184	8975001-507		182-184	8975001-507			
	5000	Consult factory		213-215	8975001-507		213-215	8975001-507			
16x16x15L	364-365	Consult factory	3x3x6	254-256	8975001-507	4x4x8	254-256	8975001-507			
	404-405	Consult factory		284-286	8975001-537		284-286	8975001-537			
	444-449	Consult factory		324-326	8975001-537		324-326	8975001-537			
	5000	Consult factory		364-405	8975001-537		364-405	8975001-537			
16x16x15L	364-365	Consult factory	3x3x6	284-286	8975001-507	4x4x8	404-405	8975001-537			
	404-405	Consult factory		143-145	8975001-507		143-145	8975001-507			
	444-449	Consult factory		182-184	8975001-507		182-184	8975001-507			
	5000	Consult factory		213-215	8975001-507		213-215	8975001-507			

PUMP SIZE	FRAME	PART NUMBER		PUMP SIZE	FRAME	PART NUMBER		PUMP SIZE	FRAME	PART NUMBER	
		A2				A2				A2	
5x5x11.5	182-184	8975001-507		6x6x13	213-215	8975001-537		8x8x13	182-184	8975001-537	
	213-215	8975001-507			254-256	8975001-537			213-215	8975001-537	
	254-256	8975001-507			284-286	8975001-537			254-256	8975001-537	
	284-286	8975001-537			324-326	8975001-537			284-286	8975001-537	
	324-326	8975001-537			364-365	8975001-537			324-326	8975001-537	
5x5x13	182-184	8975001-537		6x6x13H	213-215	8975001-537		8x8x13L	364-365	8975001-537	
	213-215	8975001-537			254-256	8975001-537			404-405	8975001-577	
	254-256	8975001-537			284-286	8975001-537			444-445	8975001-577	
	284-286	8975001-537			324-326	8975001-537			447-449	8975001-577	
	324-326	8975001-537			364-365	8975001-537			182-184	8975001-537	
5x5x13H	364-365	8975001-537		6x6x13L	404-405	8975001-577		8x8x15L	213-215	8975001-537	
	182-184	8975001-537			444-445	8975001-577			254-256	8975001-537	
	213-215	8975001-537			447-449	8975001-577			284-286	8975001-537	
	254-256	8975001-537			213-215	8975001-537			324-326	8975001-537	
	284-286	8975001-537			254-256	8975001-537			364-365	8975001-577	
5x5x8	324-326	8975001-537		6x6x6	284-286	8975001-537		8x8x15	404-405	8975001-577	
	364-365	8975001-537			324-326	8975001-537			444-445	8975001-577	
	143-145	8975001-507			364-365	8975001-537			447-449	8975001-577	
	182-184	8975001-507			143-145	8975001-507			284-286	8975001-577	
	213-215	8975001-507			182-184	8975001-507			324-326	8975001-577	
6x6x10	254-256	8975001-507		6x6x8	213-215	8975001-507		8x8x15L	364-365	8975001-577	
	284-286	8975001-537			254-256	8975001-507			404-405	8975001-577	
	324-326	8975001-537			284-286	8975001-537			444-445	8975001-577	
	364-365	8975001-537			213-215	8975001-507			447-449	8975001-577	
	404-405	8975001-537			254-256	8975001-507			284-286	8975001-577	
6x6x11.5	444-445	8975001-537		8x8x10	284-286	8975001-537		8x8x8	324-326	8975001-577	
	447-449	8975001-537			324-326	8975001-537			364-365	8975001-577	
	182-184	8975001-507			254-256	8975001-507			404-405	8975001-577	
	213-215	8975001-507			284-286	8975001-537			444-445	8975001-577	
	254-256	8975001-507			324-326	8975001-537			447-449	8975001-577	
6x6x11.5	284-286	8975001-537		8x8x11.5	364-365	8975001-537		8x8x8	182-184	8975001-507	
	324-326	8975001-537			404-405	8975001-537			213-215	8975001-507	
	364-365	8975001-537							254-256	8975001-507	
									284-286	8975001-537	

APPLICATION GUIDE

Fluid	<=200F			>200F AND <=250F			>250F AND <=275F			>275F
	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	ANY PPM
Potable Water	A1-2/D4*	No Potable water under this condition								
Non-potable Water	A1-2/D4*	A3/D3*	NCP	A4/D3*	A4/D3*	NCP	A4/NCP*	NCP	NCP	NCP
Glycol >30%	G30/D4*	NCP	NCP	G30/D4*	NCP	NCP	G30/NCP*	NCP	NCP	NCP
All other	A1-2/D4*	A3/D3*	NCP	A4/D3*	A4/D3*	NCP	A4/NCP*	NCP	NCP	NCP

*16x16x19 IEC355/NEMA500 and up, 20x20x19

4302 REPLACEMENT SEAL - OUTSIDE**REPLACEMENT SEAL PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
3x3x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
3x3x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
3x3x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
4x4x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
4x4x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-254	8975002-304	8975000-962	8975002-408	8975002-405
4x4x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
6x6x10	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
6x6x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-284	8975002-304	8975000-962	8975002-408	8975002-405
6x6x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
8x8x10	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
	444-445	8975002-334	8975000-963	8975002-438	8975002-435
8x8x11.5	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
8x8x13	182-184	8975002-334	8975000-963	8975002-438	8975002-435
	213-215	8975002-334	8975000-963	8975002-438	8975002-435
	254-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
8x8x8	182-184	8975002-304	8975000-962	8975002-408	8975002-405
	213-215	8975002-304	8975000-962	8975002-408	8975002-405
	254-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435

4302 REPLACEMENT SEAL KIT - OUTSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
3x3x10	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
3x3x6	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
3x3x8	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
4x4x10	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
4x4x6	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-254	8975002-304K	-	-	-
4x4x8	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
6x6x10	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
6x6x6	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-284	8975002-304K	-	-	-
6x6x8	143-145	8975002-304K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
8x8x10	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
	444-445	8975002-334K	-	-	-

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
8x8x11.5	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
	8x8x13	182-184	8975002-334K	-	-
213-215		8975002-334K	-	-	-
254-256		8975002-334K	-	-	-
284-286		8975002-334K	-	-	-
324-326		8975002-334K	-	-	-
364-365		8975002-334K	-	-	-
404-405		8975002-334K	-	-	-
8x8x8	444-444	8975002-334K	-	-	-
	182-184	8975002-304K	-	-	-
	213-215	8975002-304K	-	-	-
	254-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-

4302 REPLACEMENT SEAL - INSIDE

REPLACEMENT SEAL PART NUMBERS

PUMP SIZE	FRAME	PART NUMBER	PUMP SIZE	FRAME	PART NUMBER	PUMP SIZE	FRAME	PART NUMBER
		A2			A2			A2
3x3x10	143-145	8975001-507	4x4x10	143-145	8975001-507	6x6x10	182-184	8975001-507
	182-184	8975001-507		182-184	8975001-507		213-215	8975001-507
	213-215	8975001-507		213-215	8975001-507		254-256	8975001-507
	254-256	8975001-507		254-256	8975001-507		284-286	8975001-537
	284-286	8975001-537		284-286	8975001-537		324-326	8975001-537
	324-326	8975001-537		324-326	8975001-537		364-365	8975001-537
	364-365	8975001-537		364-365	8975001-537		404-405	8975001-537
	404-405	8975001-537		404-405	8975001-537			
3x3x6	143-145	8975001-507	4x4x6	143-145	8975001-507	6x6x6	143-145	8975001-507
	182-184	8975001-507		182-184	8975001-507		182-184	8975001-507
	213-215	8975001-507		213-254	8975001-507		213-215	8975001-507
3x3x8	143-145	8975001-507	4x4x8	143-145	8975001-507	6x6x8	254-284	8975001-507
	182-184	8975001-507		182-184	8975001-507		143-145	8975001-507
	213-215	8975001-507		213-215	8975001-507		182-184	8975001-507
	254-256	8975001-507		254-256	8975001-507		213-215	8975001-507
	284-286	8975001-537		284-286	8975001-537		254-256	8975001-507
		324-326	8975001-537	284-286	8975001-537	324-326	8975001-537	
						364-365	8975001-537	

PARTS LIST Vertical In-line Pump

26

PUMP SIZE	FRAME	PART NUMBER A2	PUMP SIZE	FRAME	PART NUMBER A2
8x8x10	213-215	8975001-507	8x8x13	182-184	8975001-537
	254-256	8975001-507		213-215	8975001-537
	284-286	8975001-537		254-256	8975001-537
	324-326	8975001-537		284-286	8975001-537
	364-365	8975001-537		324-326	8975001-537
	404-405	8975001-537		364-365	8975001-537
	444-445	8975001-537		404-405	8975001-537
8x8x11.5	213-215	8975001-507	8x8x8	182-184	8975001-507
	254-256	8975001-507		213-215	8975001-507
	284-286	8975001-537		254-256	8975001-507
	324-326	8975001-537		284-286	8975001-537
	364-365	8975001-537			
	404-405	8975001-537			

APPLICATION GUIDE										
Fluid	<=200F			>200F AND <=250F			>250F AND <=275F			>275F
	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	ANY PPM
Potable Water	A1-2	No Potable water under this condition								
Non-potable Water	A1-2	A3	NCP	A4	A4	NCP	A4	NCP	NCP	NCP
Glycol >30%	G30	NCP	NCP	G30	NCP	NCP	G30	NCP	NCP	NCP
All other	A1-2	A3	NCP	A4	A4	NCP	A4	NCP	NCP	NCP

4312 REPLACEMENT SEAL - OUTSIDE**REPLACEMENT SEAL PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
2x2x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
2x2x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-215	8975002-304	8975000-962	8975002-408	8975002-405
2x2x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
3x3x10	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
3x3x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-304	8975000-962	8975002-408	8975002-405
3x3x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
4x4x10	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
4x4x13	213-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
4x4x6	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-304	8975000-962	8975002-408	8975002-405
4x4x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
5x5x13	213-256	8975002-334	8975000-963	8975002-438	8975002-435
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435
6x6x8	143-145	8975002-304	8975000-962	8975002-408	8975002-405
	182-256	8975002-304	8975000-962	8975002-408	8975002-405
	284-286	8975002-334	8975000-963	8975002-438	8975002-435
	324-326	8975002-334	8975000-963	8975002-438	8975002-435
	364-365	8975002-334	8975000-963	8975002-438	8975002-435
	404-405	8975002-334	8975000-963	8975002-438	8975002-435

4312 REPLACEMENT SEAL KIT - OUTSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER			
		A1-2	G30	A3	A4
2x2x10	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
2x2x6	143-145	8975002-304K	-	-	-
	182-215	8975002-304K	-	-	-
2x2x8	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
3x3x10	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
3x3x6	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-304K	-	-	-
3x3x8	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
4x4x10	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
4x4x13	213-256	8975002-334K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
4x4x6	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-304K	-	-	-
4x4x8	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
5x5x13	213-256	8975002-334K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-
6x6x8	143-145	8975002-304K	-	-	-
	182-256	8975002-304K	-	-	-
	284-286	8975002-334K	-	-	-
	324-326	8975002-334K	-	-	-
	364-365	8975002-334K	-	-	-
	404-405	8975002-334K	-	-	-


4312 REPLACEMENT SEAL - INSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER
		A2
2x2x10	143-145	8975001-507
	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
2x2x6	143-145	8975001-507
	182-215	8975001-507
2x2x8	143-145	8975001-507
	182-256	8975001-507
	284-286	8975001-537
3x3x10	143-145	8975001-507
	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
	364-365	8975001-537
3x3x6	143-145	8975001-507
	182-256	8975001-507
	284-286	8975001-507
3x3x8	143-145	8975001-507
	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
4x4x10	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
	364-365	8975001-537
	404-405	8975001-537
	213-256	8975001-537
4x4x13	284-286	8975001-537
	324-326	8975001-537
	364-365	8975001-537
	143-145	8975001-507
	182-256	8975001-507
4x4x6	182-256	8975001-507
	284-286	8975001-507
	143-145	8975001-507
4x4x8	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
	213-256	8975001-537
5x5x13	284-286	8975001-537
	324-326	8975001-537
	364-365	8975001-537
	404-405	8975001-537
	143-145	8975001-507
6x6x8	182-256	8975001-507
	284-286	8975001-537
	324-326	8975001-537
	364-365	8975001-537
	404-405	8975001-537
	143-145	8975001-507

APPLICATION GUIDE

Fluid	<=200F			>200F AND <=250F			>250F AND <=275F			>275F
	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	<=2000 PPM	>2000PPM & <=4000PPM	>4000 PPM	ANY PPM
Potable Water	A1-2	No Potable water under this condition								
Non-potable Water	A1-2	A3	NCP	A4	A4	NCP	A4	NCP	NCP	NCP
Glycol >30%	G30	NCP	NCP	G30	NCP	NCP	G30	NCP	NCP	NCP
All other	A1-2	A3	NCP	A4	A4	NCP	A4	NCP	NCP	NCP

4380, 4382 & 4392 MECHANICAL SEAL KIT - INSIDE



KIT CONTENTS

ITEM	DESCRIPTION
(25)	Casing Gasket
(28)	Impeller Capscrew
(27)	Impeller Washer
(26)	Mechanical Seal Kit

4380, 4382 & 4392 REPLACEMENT SEAL KIT - INSIDE



KIT CONTENTS

ITEM	DESCRIPTION
(25)	Casing Gasket
(26)	Impeller Capscrew
(27)	Impeller Washer
(28)	Mechanical Seal

Manu Code	ACssc O EPSS 2A	C-ssc L EPSS 2A	SSCssc L EPSS 2A
Seal type	2A		
Rotating Face	Antimony Loaded Carbon	Resin Bonded Carbon	Sintered Silicon Carbide
Stationary Seat	Sintered Silicon Carbide		
Seat Elastomer	EPDM (O-RING)	EPDM (L-CUP)	EPDM (L-CUP)
Secondary Seal	EPDM	EPDM	EPDM
Legend (Refer App.Guide)	H3-A	L1-A	L2-A

4380 REPLACEMENT SEAL

REPLACEMENT SEAL PART NUMBERS

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
3x3x6B	143JM-184JM	89975001-813	8975000-982	89975001-817
3x3x6B	215JP	89975001-813	8975000-982	89975001-817
3x3x6B	254JM-256JM	89975001-833	8975000-984	89975001-837
3x3x6B	284JM-286JM	89975001-833	8975000-984	89975001-837
4x4x6C	143JM-184JM	89975001-813	8975000-982	89975001-817
4x4x6C	213JM-215JP	89975001-813	8975000-982	89975001-817
4x4x6C	254JM-256JM	89975001-833	8975000-984	89975001-837
4x4x6C	284JM-286JM	89975001-833	8975000-984	89975001-837
4x4x6C	324JM	89975001-833	8975000-984	89975001-837
5x5x6	143JM-184JM	89975001-813	8975000-982	89975001-817
5x5x6	213JM-215JP	89975001-813	8975000-982	89975001-817
5x5x6	256JM	89975001-833	8975000-984	89975001-837
5x5x6	284JM-286JM	89975001-833	8975000-984	89975001-837
5x5x6	324JM-326JM	89975001-833	8975000-984	89975001-837



4380 REPLACEMENT SEAL KIT - INSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
1.5x1.5x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
1.5x1.5x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
2x2x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
2x2x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
2x2x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
3x3x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
3x3x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
3x3x5L	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
3x3x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
	284-326	89975001-83301K	8975000-98401K	89975001-83701K
3x3x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
4x4x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
4x4x11.5	143-184	89975001-81304K	8975000-98204K	89975001-81704K
	213-215	89975001-83304K	8975000-98404K	89975001-83704K
	254-256	89975001-83304K	8975000-98404K	89975001-83704K
	284-286	89975001-83304K	8975000-98404K	89975001-83704K

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
4x4x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
4x4x13L	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
4x4x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
4x4x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
5x5x11.5	143-184	89975001-81304K	8975000-98204K	89975001-81704K
	213-215	89975001-83304K	8975000-98404K	89975001-83704K
	254-256	89975001-83304K	8975000-98404K	89975001-83704K
	284-286	89975001-83304K	8975000-98404K	89975001-83704K
5x5x13	182-184	89975001-83305K	8975000-98405K	89975001-83705K
	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-286	89975001-83305K	8975000-98405K	89975001-83705K
	324-326	89975001-83305K	8975000-98405K	89975001-83705K
	364-365	89975001-83305K	8975000-98405K	89975001-83705K
5x5x13H	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-286	89975001-83305K	8975000-98405K	89975001-83705K
	324-326	89975001-83305K	8975000-98405K	89975001-83705K
	364-365	89975001-83305K	8975000-98405K	89975001-83705K
5x5x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
6x6x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
6x6x11.5	143-184	89975001-81304K	8975000-98204K	89975001-81704K
	213-215	89975001-83304K	8975000-98404K	89975001-83704K
	254-256	89975001-83304K	8975000-98404K	89975001-83704K
	284-326	89975001-83304K	8975000-98404K	89975001-83704K
6x6x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
6x6x13H	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-286	89975001-83305K	8975000-98405K	89975001-83705K
	324-326	89975001-83305K	8975000-98405K	89975001-83705K
	364-365	89975001-83305K	8975000-98405K	89975001-83705K
	404-405	89975001-87305K	8975000-98505K	89975001-87705K
	444-445	89975001-87305K	8975000-98505K	89975001-87705K
	447-449	89975001-87305K	8975000-98505K	89975001-87705K

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
6x6x6	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
6x6x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
8x8x10	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
8x8x11.5	143-184	89975001-81304K	8975000-98204K	89975001-81704K
	213-215	89975001-83304K	8975000-98404K	89975001-83704K
	254-256	89975001-83304K	8975000-98404K	89975001-83704K
	284-326	89975001-83304K	8975000-98404K	89975001-83704K
8x8x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
8x8x13L	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
8x8x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K
2.5x2.5x7.5	254JM	89975001-83302K	8975000-98402K	89975001-83702K
	256JM	89975001-83302K	8975000-98402K	89975001-83702K
	284JM	89975001-83302K	8975000-98402K	89975001-83702K
	286JM	89975001-83302K	8975000-98402K	89975001-83702K
3x3x7.5	254JM	89975001-83302K	8975000-98402K	89975001-83702K
	256JM	89975001-83302K	8975000-98402K	89975001-83702K
	284JM	89975001-83302K	8975000-98402K	89975001-83702K
	286JM	89975001-83302K	8975000-98402K	89975001-83702K
	324JM	89975001-83302K	8975000-98402K	89975001-83702K
	326JM	89975001-83302K	8975000-98402K	89975001-83702K
5x5x7.5	284JM	89975001-83302K	8975000-98402K	89975001-83702K
	286JM	89975001-83302K	8975000-98402K	89975001-83702K
	324JM	89975001-83302K	8975000-98402K	89975001-83702K
	326JM	89975001-83302K	8975000-98402K	89975001-83702K

APPLICATION GUIDE

Fluid	<200F			>200F		
	<=2000PPM	>2000PPM	>4000PPM	<=2000PPM	>2000PPM	>4000PPM
Potable Water	L1-A	No potable water for this application				
Non-Potable Water	L1-A	L2-A	NCP	H3-A	L2-A	NCP
Glycol > 30%	L2-A	NCP	NCP	L2-A	L2-A	NCP
All Other	L1-A	L2-A	NCP	H3-A	L2-A	NCP

4382 REPLACEMENT SEAL KIT - INSIDE**KIT PART NUMBERS**

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
3x3x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
3x3x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
3x3x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
4x4x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
4x4x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
4x4x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-286	89975001-83302K	8975000-98402K	89975001-83702K
6x6x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-286	89975001-83303K	8975000-98403K	89975001-83703K
	324-326	89975001-83303K	8975000-98403K	89975001-83703K
6x6x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
6x6x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-286	89975001-83302K	8975000-98402K	89975001-83702K
	324-326	89975001-83302K	8975000-98402K	89975001-83702K
8x8x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-286	89975001-83303K	8975000-98403K	89975001-83703K
	324-326	89975001-83303K	8975000-98403K	89975001-83703K

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
8x8x11.5	182-184	89975001-81304K	8975000-98204K	89975001-81704K
	213-215	89975001-83304K	8975000-98404K	89975001-83704K
	254-256	89975001-83304K	8975000-98404K	89975001-83704K
	284-326	89975001-83304K	8975000-98404K	89975001-83704K
8x8x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
8x8x13L	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
8x8x8	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K

APPLICATION GUIDE						
Fluid	<200F			>200F		
	<=2000PPM	>2000PPM	>4000PPM	<=2000PPM	>2000PPM	>4000PPM
Potable Water	L1-A	No potable water for this application				
Non-Potable Water	L1-A	L2-A	NCP	H3-A	L2-A	NCP
Glycol > 30%	L2-A	NCP	NCP	L2-A	L2-A	NCP
All Other	L1-A	L2-A	NCP	H3-A	L2-A	NCP

4392 REPLACEMENT SEAL KIT - INSIDE

KIT PART NUMBERS

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
2x2x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
2x2x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
2x2x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
3x3x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
	284-326	89975001-83303K	8975000-98403K	89975001-83703K
3x3x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
3x3x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
4x4x10	143-184	89975001-81303K	8975000-98203K	89975001-81703K
	213-215	89975001-83303K	8975000-98403K	89975001-83703K
	254-256	89975001-83303K	8975000-98403K	89975001-83703K
4x4x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
4x4x6	56	89975001-81301K	8975000-98201K	89975001-81701K
	143-184	89975001-81301K	8975000-98201K	89975001-81701K
	213-215	89975001-81301K	8975000-98201K	89975001-81701K
	254-256	89975001-83301K	8975000-98401K	89975001-83701K
4x4x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
4x4x8	284-326	89975001-83302K	8975000-98402K	89975001-83702K

PUMP SIZE	FRAME	PART NUMBER		
		H3-A	L1-A	L2-A
5x5x13	213-215	89975001-83305K	8975000-98405K	89975001-83705K
	254-256	89975001-83305K	8975000-98405K	89975001-83705K
	284-326	89975001-83305K	8975000-98405K	89975001-83705K
6x6x8	56	89975001-81302K	8975000-98202K	89975001-81702K
	143-184	89975001-81302K	8975000-98202K	89975001-81702K
	213-215	89975001-83302K	8975000-98402K	89975001-83702K
	254-256	89975001-83302K	8975000-98402K	89975001-83702K
	284-326	89975001-83302K	8975000-98402K	89975001-83702K


APPLICATION GUIDE

Fluid	<200F			>200F		
	<=2000PPM	>2000PPM	>4000PPM	<=2000PPM	>2000PPM	>4000PPM
Potable Water	L1-A	No potable water for this application				
Non-Potable Water	L1-A	L2-A	NCP	H3-A	L2-A	NCP
Glycol > 30%	L2-A	NCP	NCP	L2-A	L2-A	NCP
All Other	L1-A	L2-A	NCP	H3-A	L2-A	NCP

STANDARD FLUSH LINE REPLACEMENT PARTS AND KITS

BRAID HOSE

PUMP SERIES	PUMP SIZE	PART NUMBER	LENGTH
4300	1.5x1.5x10	8939031-715	15
4300	1.5x1.5x6	8939031-715	15
4300	1.5x1.5x8	8939031-715	15
4300	10x10x15	8939031-730	30
4300	2x2x10	8939031-715	15
4300	2x2x6	8939031-715	15
4300	2x2x8	8939031-715	15
4300	2.5x2.5x7.5	8939031-720	20
4300	3x3x7.5	8939031-720	20
4300	3x3x10	8939031-715	15
4300	3x3x13	8939031-720	20
4300	3x3x6	8939031-715	15
4300	4x4x10	8939031-720	20
4300	4x4x11.5	8939031-720	20
4300	4x4x13	8939031-720	20
4300	4x4x13L	8939031-720	20
4300	4x4x6	8939031-715	15



PUMP SERIES	PUMP SIZE	PART NUMBER	LENGTH
4300	4x4x8	8939031-715	15
4300	5x5x7.5	8939031-720	20
4300	5x5x11.5	8939031-720	20
4300	5x5x8	8939031-720	20
4300	6x6x10	8939031-720	20
4300	6x6x11.5	8939031-720	20
4300	6x6x6	8939031-715	15
4300	6x6x8	8939031-720	20
4300	8x8x10	8939031-720	20
4300	8x8x11.5	8939031-720	20
4300	8x8x15	8939031-730	30
4300	8x8x15L	8939031-730	30
4300	8x8x8	8939031-720	20
4302	3x3x10	8939031-715	15
4302	3x3x6	8939031-715	15
4302	3x3x8	8939031-715	15
4302	4x4x10	8939031-715	15
4302	4x4x6	8939031-715	15
4302	4x4x8	8939031-715	15
4302	6x6x10	8939031-715	15
4302	6x6x6	8939031-715	15
4302	6x6x8	8939031-715	15
4302	8x8x10	8939031-715	15
4302	8x8x11.5	8939031-715	15
4302	8x8x8	8939031-715	15
4302	3x3x10	8939031-715	15
4302	3x3x6	8939031-715	15

PUMP SERIES	PUMP SIZE	PART NUMBER	LENGTH
4302	3x3x8	8939031-715	15
4302	4x4x10	8939031-715	15
4302	4x4x6	8939031-715	15
4302	4x4x8	8939031-715	15
4302	6x6x10	8939031-715	15
4302	6x6x6	8939031-715	15
4302	6x6x8	8939031-715	15
4302	8x8x10	8939031-715	15
4302	8x8x11.5	8939031-720	20
4302	8x8x8	8939031-715	15
4302	6x6x10	8939031-720	20
4302	8x8x10	8939031-720	20
4312	2x2x10	8939031-720	20
4312	3x3x10	8939031-720	20
4312	3x3x8	8939031-720	20
4312	4x4x13	8939031-730	30
4312	4x4x6	8939031-720	20
4312	4x4x8	8939031-720	20
4312	5x5x13	8939031-735	35
4312	2x2x10	8939031-715	15
4312	2x2x6	8939031-715	15
4312	3x3x6	8939031-715	15
4312	4x4x13	8939031-720	20
4312	4x4x6	8939031-715	15
4312	4x4x8	8939031-720	20
4312	6x6x8	8939031-720	20

FLUSH LINE FASTENERS PARTS

ITEM NUMBER	DESCRIPTION
8938203-701	NIPPLE SS304 ¼NPT x 2.500"
8938208-001	NIPPLE SST ¼NPT x 5.000" LG
8939031-075	ADAPTER-S SS 0.5" JICM-0.25" NPTM
8935102-701	CROSS-90° SST ¼NPT
8934210-701	ELBOW-ST 90° SS316 ¼NPT
8934201-701	TEE-90° SS304 ¼NPT
8939018-302	VENT-AIR SS316 ¼NPT
89076100-001	BALL VALVE M/F

SPARE FILTER-CARTRIDGE

PUMP SIZE	PART NUMBER
2.5x2.5x7.5	8975000-303
3x3x7.5	8975000-303
5x5x7.5	8975000-303




FLUSH LINE FASTENERS KIT

DESCRIPTION	ITEM NUMBER	KIT COMPONENT
Small Single 4300 Pump	89981000-078K	Nipple
		Tee-90°
		Air - Vent
		Adapter
Large Double 4300 Pump	89981000-079K	Nipple
		Tee-90°
		Air - Vent
		Elbow
		Adapter
4382 - dualArm Pump	89981000-078K (Discharge)	Nipple
		Tee-90°
		Air - Vent
		Adapter
	89076100-001K (Suction)	Ball Valve
	Adapter	
4392 - Twin Pump	89981000-082K	Nipple
		Tee-90°
		Air - Vent
		Elbow
		Adapter


KIT CONTENTS

ITEM	DESCRIPTION
(29)	AIR-VENT ¼NPT
(30)	TEE-90° ¼NPT
(31)	ADAPTER 0.5"JICM - 0.25"NPTM
(32)	NIPPLE ¼NPT
(33)	ELBOW 90° ¼NPT
(34)	CROSS-90° SST ¼NPT
(35)	BALL VALVE M/F


89981000-000K




89981000-078K



89981000-079K



89981000-082K



TORONTO

23 BERTRAND AVENUE,
TORONTO, ONTARIO,
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE, NORTH
TONAWANDA, NEW YORK,
USA, 14120-6594
+1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS
BUSINESS PARK, DROITWICH SPA,
WORCESTERSHIRE,
UNITED KINGDOM, WR9 0LW
+44 121 550 5333

MANCHESTER

WOLVERTON STREET, MANCHESTER
UNITED KINGDOM, M11 2ET
+44 161 223 2223

BANGALORE

#18, LEWIS WORKSPACE, 3RD FLOOR,
OFF MILLERS - NANDIDURGA ROAD,
JAYAMAHAL CBD, BENSON TOWN,
BANGALORE, INDIA 560 046
+91 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

BEIJING

ROOM 1612, NANYIN BUILDING NO.2
NORTH EAST THRID RING ROAD
CHAOYANG DISTRICT, BEIJING,
CHINA 100027
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES
AGOSTINHO, 1370 GALPÃO 6 EMBU
DAS ARTES, SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O. BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

FRANKFURT

WESTERBACHSTRASSE 32,
D-61476 KRONBERG IM TAUNUS
GERMANY
+49 6173 999 77 55

FOR SERVICE RELATED PARTS & KITS

Use ADEPT Select to quickly and easily select.
Visit adept.armstrongfluidtechnology.com to learn more



FOR MORE INFORMATION,

Contact your Armstrong Representative or visit us at
ArmstrongFluidTechnology.com/ContactUs

