

## VORTEX AIR SEPARATORS | MODELS VA/VAS | INSTALLATION AND OPERATING INSTRUCTIONS


File No: 37.875  
Date: SEPTEMBER 22, 2016  
Supersedes: 37.875  
Date: SEPTEMBER 05, 2003

Sizes: 14" to 24" - Fabricated C. Steel

### 1.0 VESSEL DESCRIPTION

Armstrong VA/VAS Vortex Air Separators eliminate air quickly and efficiently from heating/cooling systems. Water enters and exits through unique **tangential** connections which promote a low velocity swirling effect in the centre of the unit. Centrifugal force moves the water to the outer edges of the unit and a vortex is formed. Entrained air migrates to the eye of the vortex (lower pressure point) and is evacuated at the top of the separator. The water exits the unit near the bottom of the unit, bubble free, protecting the system against the noise, corrosion and damage associated with entrained air.

VAS models are equipped with a stainless steel strainer.



### 2.0 CONSTRUCTION DETAILS

#### Materials of construction

**Shell:** Fabricated steel

**Strainer:** Stainless steel mesh (¼"× ¾")

**Gasket:** Non-asbestos

#### Technical data

**Max. working temperature:** 450°F (232°C)

**Max. working pressure:** 125 PSI (865 kPa)

**Connection type:** 150# Flanged ANSI (RFSO)

### 3.0 STEPS & PROCEDURE

- Visually inspect the air separator for damage, which may occur during transit.
- A manual drain can be added to help facilitate purging sediment from the air separator.
- VAS models have a strainer that must be removed and cleaned after 24 hours of operation.

DISTANCE REQUIRED TO REMOVE STRAINER	
SIZE	DISTANCE inch (mm)
VAS 14	46 (1168)
VAS 16	60 (1524)
VAS 18	67 (1701)
VAS 20	72 (1829)
VAS 22	80 (2032)
VAS 24	85 (2159)

**TORONTO**

23 BERTRAND AVENUE  
TORONTO, ONTARIO  
CANADA  
M1L 2P3  
+1 416 755 2291

**BUFFALO**

93 EAST AVENUE  
NORTH TONAWANDA, NEW YORK  
U.S.A.  
14120-6594  
+1 716 693 8813

**BIRMINGHAM**

HEYWOOD WHARF, MUCKLOW HILL  
HALESOWEN, WEST MIDLANDS  
UNITED KINGDOM  
B62 8DJ  
+44 (0) 8444 145 145

**MANCHESTER**

WOLVERTON STREET  
MANCHESTER  
UNITED KINGDOM  
M11 2ET  
+44 (0) 8444 145 145

**BANGALORE**

#59, FIRST FLOOR, 3RD MAIN  
MARGOSA ROAD, MALLESWARAM  
BANGALORE, INDIA  
560 003  
+91 (0) 80 4906 3555

**SHANGHAI**

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP  
FENG XIAN DISTRICT, SHANGHAI  
P.R.C.  
201401  
+86 21 3756 6696

**SÃO PAULO**

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,  
1370 GALPÃO 6  
EMBU DAS ARTES  
SAO PAULO, BRAZIL  
+55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY  
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

**MAKING  
ENERGY  
MAKE  
SENSE™**