

IPS Controller 3000

SUBMITTAL

JOB: _____	REPRESENTATIVE: _____
_____	_____
ENGINEER: _____	ORDER NO: _____ DATE: _____
CONTRACTOR: _____	SUBMITTED BY: _____ DATE: _____
_____	APPROVED BY: _____ DATE: _____

SYSTEM LAYOUT / CONFIGURATION

Number of pumps being controlled: _____ (Specify 1 to 4)

Number of remote DP/Temperature/Flow signals (zones): _____ (Specify 1 to 5)

IPS CONTROLLER 3000 VARIANT

	Input Zone Capability	Output Pump Control Capability	Select Standby or Parallel Operation of Pumps (VFDs)
IPS3001	up to 2 Zones	up to 3 pumps	<input type="checkbox"/> IPS3001 Standby <input type="checkbox"/> IPS3001 Parallel
IPS3002	up to 5 Zones	up to 4 pumps	<input type="checkbox"/> IPS3002 Standby <input type="checkbox"/> IPS3002 Parallel



STANDARD FUNCTIONALITY and CONSTRUCTION

- 4-row x 20-character LCD & keypad interface
- On-screen menu driven operator interface
- Manual or automatic system control (H-O-A selection)
- Remote or local start/stop mode of operation
- 2-level (field and factory) password security
- Fault memory and alarm history
- Adjustable PID control loop
- UL Listed and CSA Certification
- Internal circuit breaker protection
- Automatic or manual pump alternation
- End-of-curve pump run-out protection
- 3 standard alarms: (1) drive, motor overload or pump failure, (2) zone signal fault, (3) any system fault
- Logic outputs for VFD automatic by-pass control
- Digital inputs for pump differential pressure switches
- Output for remote alarm/horn signal
- Input for silencer of remote alarm/horn
- Separate input screen for remote zone DP/temperature/flow sensor setpoints
- Separate input screen for input of DP/temperature/flow operating range
- Separate operating pump display status, pump speed(s) and drive status
- Separate status screen of remote zone signals, zone faults, zone setpoint and active control zone
- Embedded logic to prevent hunting, pump flow surge and motor overloading
- Manual control screen for fixed speed, by-pass, or selected variable speed settings
- Key lockable front cabinet door

DIMENSIONS and WEIGHTS

Model	Width	Height	Depth	Weight
IPS Controller 3000	20 (508)	20 (508)	8 (203)	60 (27)

Note: Dimensions are in inches (mm). Weights are in lbs. (kg).

POWER SUPPLY

Volts	Frequency	Phase
<input type="checkbox"/> 115 Vac	60 Hz	single
<input type="checkbox"/> 230 Vac		
<input type="checkbox"/> 240 Vac	50 Hz	

ENCLOSURE DETAILS

- NEMA 1
- NEMA 2
- NEMA 4
- NEMA 12
- EEMAC 2

OPTIONS and ACCESSORIES

- A serial communications port for integration into a Building Automation System (standard communication options included with basic system are Modbus, LonWorks, Trend, MetaSys and pLAN)
- Serial communications port to receive full information from the variable speed drives (Modbus)
- Optional communications gateways for BACNet, and Webgate (TCP/IP)
- Armstrong shall enter the project specific field enter parameters
- Telephone communications modem and port
- Flash memory card, expandable to 4 MB

S. A. Armstrong Limited
23 Bertrand Avenue
Toronto, Ontario
Canada, M1L 2P3
T: (416) 755-2291
F (Main): (416) 759-9101

Armstrong Pumps Inc.
93 East Avenue
North Tonawanda, New York
U.S.A. 14120-6594
T: (716) 693-8813
F: (716) 693-8970

Armstrong Holden Brooke Pullen
Wenlock Way
Manchester
United Kingdom, M12 5JL
T: +44 (0) 1612 232223
F: +44 (0) 1612 209660

