

Wafer Check Valves


FILE NO: 62.745
DATE: Sep. 03, 2010
SUPERSEDES: New
DATE: New

SUBMITTAL

JOB:	REPRESENTATIVE:	REPRESENTATIVE:	
	ORDER NO:	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	

MATERIALS OF CONSTRUCTION					
1	Cast Body	A126 Class B			
2	Plug	A351 Gr. CF8M			
3	Spring	Stainless Steel			
4	Seat	A351 Gr. CF8M			
5	Bushing	Stainless Steel			
6	Screw	Stainless Steel			

PRESSURES AND TEMPERATURES					
Service	psi	Temperature			
Liquid	200	82°C (180°F)			



DIMENSION				
Size	Α	В	Cv	Weight
2.50 (65)	2.88 (73)	4.75 (121)	60	9 (4.1)
3.00 (80)	3.13 (80)	5.25 (133)	85	15 (6.8)

Note: All measurements are in inches (mm) and weights are in lbs (kg).

Notes: Manufacturer reserves the right to modify dimensions, materials, or design. Contact factory for certification.

The Flow Coefficient (Cv) is the number of gallons per minute of water flowing through a given size restriction at a pressure drop of one psi.

S. A. Armstrong Limited 23 Bertrand Avenue Toronto, Ontario

Canada, M1L 2P3 T: (416) 755-2291 F (Main): (416) 759-9101 Armstrong Pumps Inc.

93 East Avenue North Tonawanda, New York U.S.A. 14120-6594 T: (716) 693-8813 F: (716) 693-8970 **Armstrong Integrated Limited**

Wenlock Way Manchester United Kingdom, M12 5JL T.: +44 (0) 8444 145 145 F.: +44 (0) 8444 145 146

