

DESIGN ENVELOPE 4300 VIL 0308-007.5 SUBMITTAL

Armstrong seal reference number

☐ Others: __

□ c1 (a)

File No: 100.4048

Date: DECEMBER 17, 2015

Supersedes: 100.4054


Date: AUGUST 14, 2015

Job:	Repres	sentative:	
	Order	No:	Date:
Engineer:	Submi	tted by:	Date:
Contractor:	Appro	ved by:	Date:
PUMP DESIGN DATA		. CONTROLS DATA	
No. of pumps: Tag:		Sensorless Control:	Standard
Capacity:USgpm (L/s) Head: _ Liquid: Viscosit		Minimum system pressure to be maintained:	ft (m)*
Temperature: °F (°C) Specific		Orientation:	☐ L1 (default) ☐ L2 ☐ L3 ☐ L4
Suction: 3" (75mm) Dischar	ge: 3" (75mm)	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-0422-10		Protocol (optional):	☐ LonWorks®
UL STD 778 & CSA STD C22.2 NO.108 certi MOTOR DESIGN DATA HP: RPM: Frame size:		Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with Weather Shield ☐ Outdoor – UL TYPE 4X less Weather Shield
Volts: Hertz: 60 Hz Pha:		Fused disconnect switch:	
Efficiency: NEMA premium 12.12	se. 3	EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATING CON	DITIONS	Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125 175 psig at 150°F (12 bars at 65°C)		Cooling:	Fan-cooled through back channel
100 psig at 300°F (7 bars at 150°C)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
ANSI 250 375 psig at 150°F (26 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
260 psig at 300°F (21 bars at 150°C)		Digital ı∕o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
MECHANICAL CEAL DECICAL DATA		Communication port:	1-RS485, 1-USB
MECHANICAL SEAL DESIGN DATA		* * If minimum maintained evetem proce	ure is not known: Default to 40% of design head
See file no. 43.50 for standard mechanical seal details as indicated below		**The IVS 102 drive is a low harmonic d guaranty performance to any systen	Irive via built-in DC line reactors. This does not n wide harmonic specification or the costs to meet ied with the system electrical details, Armstrong

will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation

and the costs for such mitigation.

2





Confirm current performance data with Armstrong ACE Online selection software.


DIMENSION DATA

	INDOOR	OUTDOOR	
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)	
Frame size:	213	213	
Size:	3×3×8	3×3×8	
HP:	7.5	7.5	
RPM:	1800	1800	
AB:	31.74(806)	37.52(953)	
В:	6.75(171)	6.75(171)	
c:	5.80(147)	5.80(147)	
D:	10.00(254)	10.00(254)	
E:	14.73(374)	18.36(466)	
P:	12.13(308)	11.25(286)	
F:	26.73(679)	30.36(771)	
S:	12.00(305)	12.00(305)	
SD:	22.00(559)	22.00(559)	
T:	6.31(160)	6.31(160)	
XY:	28.04(712)	29.16(741)	
Weight:	326(147.9)	376(170.6)	

Dimensions - inch (mm) Weight - lbs (kg)








WEATHER

SHIELD



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM