

# **DESIGN ENVELOPE** 4300 VIL 1619-250.0 SUBMITTAL

See file no. 43.50 for standard mechanical seal details as

indicated below

☐ c1 (a)

Armstrong seal reference number


☐ Others:

File No: 100.4236 Date: DECEMBER 17, 2015 Supersedes: 100.4220 **Date:** AUGUST 14, 2015

Job:	Repre	sentative:	
			Date:
Engineer: Sul  Contractor: Ap			
		oved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps: Ta	ag:	Sensorless Control:	Standard
Capacity:USgpm (L/s) Ho		Minimum system pressure to be maintained:	ft (m)*
Temperature: °F (°C) Sp		Orientation:	□ L1 (default) □ L2 □ L3 □ L4
Suction: 16" (400 mm) Di	ischarge: 16" (400 mm)	Protocol (standard):	☐ Modbus rtu ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
MOTOR DESIGN DATA  HP: RPM: Frame size: Enclosure:  Volts: Hertz: 60 Hz Phase: 3  Efficiency: NEMA premium 12.12		Protocol (optional):	☐ LonWorks®
		Enclosure:	☐ Indoor - UL TYPE 12
		Fused disconnect switch:	N/A
		EMI/RFI control:	Integrated filter designed to meet EN61800-3
		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
		: Cooling:	Fan-cooled through back channel
MAXIMUM PUMP OPERATING CONDITIONS		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
100 psig at 300°F (7 bars at 150°C) ANSI 250		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
375 psig at 150°F (26 bars at 65°C)		Pulse inputs:	Two programmable
260 psig at 300°F (21 bars at 150°C)		Relay outputs:	Two programmable
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet	
MECHANICAL SEAL DESIGN DATA			lied with the system electrical details, Armstrong

a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

#### **DIMENSION DATA**

### INDOOR (UL TYPE 12/ODP)

(OL TIPE 12/ODF)

Frame size: 449

**Size:** 16×16×19

**HP:** 250

**RPM:** 1480

**AB:** 76.15(1934)

**B:** 22.90(582)

**c:** 15.70(399)

**D:** 36.00(914)

**E:** 25.05(636)

**P:** 22.44(570)

**F:** 25.05(636)

**s:** 36.00(914)


**sp:** 72.00(1829)

**T:** 17.80(452)

**XY:** 80.59(2047)

Weight: 6300(2857.6)

Dimensions - inch (mm) Weight - lbs (kg)



# TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

# BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM



