

# DESIGN ENVELOPE 4300 VIL | 1213-200.0 | SUBMITTAL

File No: 101.5145 Date: MARCH 24, 2017 Supersedes: 100.4168 Date: DECEMBER 17, 2015

Representative:	
Order No:	Date:
Submitted by:	_ Date:
Approved by:	_Date:
	Order No: Submitted by:

#### PUMP DESIGN DATA

No. of pumps:		Tag:		
Capacity:	USgpm (L/s)	Head:ft (m)		
Liquid:		Viscosity:		
Temperature:	°F (°C)	Specific gravity:		
Suction: 12" (300 mr	n)	Discharge: 12" (300 mm)		
OSHPD Seismic Certification OSP-0422-10				

UL STD 778 & CSA STD C22.2 NO.108 certified

#### MOTOR DESIGN DATA

HP:	RPM:	Frame size:	Enclosure:
Volts:		Hertz: 60 Hz	Phase: 3

Efficiency: NEMA premium 12.12

#### MAXIMUM PUMP OPERATING CONDITIONS

#### ANSI 125

175 psig at 150°F (12 bar at 65°C) 100 psig at 300°F (7 bar at 150°C)

ANSI 250 375 psig at 150°F (26 bar at 65°C) 260 psig at 300°F (21 bar at 150°C)

• Tolerance of ±0.125" (±3 mm) should be used

For exact installation, data please write factory for certified dimensions

#### MECHANICAL SEAL DESIGN DATA

See file no. 43.50 for standard mechanical seal details as indicated below

Armstrong seal reference number

□ c1 (a) □ Others: \_\_\_\_

# CONTROLS DATA

Orientation:	□ L1 (default) □ L2 □ L3 □ L4
Protocol (standard):	□ bacnet <sup>™</sup> ms/tp □ bacnet <sup>™</sup> tcp/ip □ Modbus rtu
Enclosure:	□ Indoor – UL TYPE 12
Fused disconnect switch:	N/A
EMI/RFI control:	Integrated filter designed to meet EN61800-3
Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
Cooling:	Fan-cooled through back channel
-	Fan-cooled through back channel -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to
Ambient temperature: Analog ı/o:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft) Two current or voltage inputs,
Ambient temperature: Analog ı/o: Digital ı/o:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft) Two current or voltage inputs, one current output Six programmable inputs (two
Ambient temperature: Analog ı/o: Digital ı/o: Pulse inputs:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft) Two current or voltage inputs, one current output Six programmable inputs (two can be configured as outputs)

\*\*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation. Design Envelope 4300 VIL

2

# OPTIONS

#### SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained

ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

# PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

# ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

 $^{\ast}\textsc{Only}$  available if sensorless bundle is enabled

# PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

\*Only available if sensorless bundle is enabled



п

п



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Controls pumps to ensure multiple zones are

• 2 sensor control - Controls pumps in a 2-zone

application to ensure both zones are always

# Cooling

**DUAL SEASON SETUP** 

ZONE OPTIMIZATION BUNDLE

satisfied for heating or cooling

satisfied for heating or cooling

Duty point \_\_\_\_\_ gpm (L/s) at \_\_\_\_\_ ft (m) Minimum system pressure to be maintained \_\_\_\_\_\_ ft (m)

## Heating

Duty point	gpm (L/s) at	ft (m)
Minimum systen	n pressure to be maint	ained
	ft (m)	

# **OPTIONAL SERVICES**

### **ON-SITE PUMP COMMISSIONING**




#### PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.


#### Available in 3 or 5 year terms


 \* Requires an internet connection to be provided by building
\* Includes an extended warranty for parts and labour (wearable parts excluded)



Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.


#### INDOOR





Dimensions – inch (mm) Weight – Ibs (kg)

#### CONTROL ORIENTATIONS



#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

#### BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

#### MANCHESTER

WOLVERTON STREET MANCHESTER UNITED KINGDOM M11 2ET +44 (0) 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

#### SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP FENG XIAN DISTRICT, SHANGHAI P.R.C. 201401 +86 21 3756 6696

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

# ENERGA SENSE SENSE