

### **DESIGN ENVELOPE 4300 VIL**

# SINGLE PHASE | 1506-001.0 | SUBMITTAL

File No: 100.4260

Date: OCTOBER 27, 2014

Supersedes: NEW


Date: NEW

Job:		Represe	entative:	
		Order N	No:	Date:
Engineer:				Date:
				Date:
PUMP DESIGN DATA		i	CONTROLS DATA	
No. of pumps:USgpm (L/		:	Power supply:	Volts: 200-240VAC Freq: 50/60Hz Phase: 1
Liquid:Osgpiii (L/		:	Sensorless Control:	
Temperature: °F (°C		:	Minimum system pressure to be maintained:	ft (m)*
Suction: 1.5" (38mm) Discharge: 1.5" (38n		nm)	Orientation:	□ L1 (default) □ L2 □ L3 □ L4
			Protocol (standard):	☐ Modbus rtu ☐ BACnet™ MS/TI☐ Johnson® N2 ☐ Siemens® FLN
MOTOR DESIGN DATA			Protocol (optional):	☐ LonWorks®
HP: 1 RPM: 1740		<u>i</u>	Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with
Enclosure: Volts: 208 Phase: 3 Efficiency:		:		Weather Shield □ Outdoor - UL TYPE 4X With  Weather Shield □ Weather Shield
			Disconnect switch:	
MAXIMUM PUMP OPERATING CONDITIONS			емі/RFI control:	1-phase IVS102 units do not meet the EN61800-3 directive
ANSI 125 175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C)			Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
ANSI 250			Cooling:	Fan-cooled through back channel
375 psig at 150°F (26 bars at 65°C 260 psig at 300°F (21 bars at 150°		:	Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		:	Analog I/o:	Two current or voltage inputs, one current output
			Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		:	Pulse inputs:	Two programmable
MECHANICAL SEAL DESIG	N DATA		Relay outputs:	Two programmable
See file no. 43.50 for standard mechanical seal details as		; ;	Communication port:	1-RS485, 1-USB
indicated below				re is not known: Default to 40% of design head rive via built-in pc line reactors. This does not
Armstrong seal reference number		:	guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details,	
☐ A1 (c) ☐ Others:				supplied with the system electrical details, lation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

 $\label{eq:mitigation} \mbox{mitigation and the costs for such mitigation.}$ 

2



Performance curves are for reference only.


 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$ 

ESTABLISHED 1934

#### **DIMENSION DATA**

	INDOOR	OUTDOOR	
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)	
Frame size:	143	143	
Size:	1.5×1.5×6	1.5×1.5×6	
HP:	1	1	
RPM:	1740	1740	
AB:	23.80(604)	29.93(760)	
В:	4.53(115)	4.53(115)	
c:	4.53(115)	4.53(115)	
D:	7.25(184)	7.25(184)	
E:	12.04(306)	17.19(437)	
F:	12.04(306)	17.19(437)	
P:	8.63(219)	7.28(185)	
s:	7.00(178)	7.00(178)	
SD:	14.25(362)	14.25(362)	
T:	4.25(108)	4.25(108)	
XY:	22.00(559)	20.50(521)	
Weight:	193(87.5)	200(90.7)	

Dimensions - inch (mm) Weight - Ibs (kg)



## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

#### BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

#### SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY

ARMSTRONGFLUIDTECHNOLOGY.COM