

DESIGN ENVELOPE 4300 VIL SINGLE PHASE | 1506-003.0 | submittal

File No: 100.4263 Date: OCTOBER 27, 2014 Supersedes: NEW Date: NEW

Job: Re;			Repre	presentative:						
			Order	r No:	Date: _					
Engineer:			Subm	itted by:	Date: _	_ Date:				
Contractor:			Appro	oved by:	Date:	Date:				
PUMP DESIGN	I DATA			CONTROLS DATA						
No. of pumps:		Tag:		Power supply:	: Volts: 200-240VAC					
	USgpm (L/s)			Sensorless Control:	Freq: 50/60Hz	Phase: 1				
	Liquid: Vis			Minimum system pressure						
Temperature: °F (•			ft (m)*				
Suction: 1.5" (38mm) Discharge: 1.5" (38mm				Orientation:	□ L1 (default) □ L2 □ L3 □ L4					
				Protocol (standard): □ Modbus rtu □ bacnet™ мs □ Johnson® ν2 □ Siemens® Fl						
MOTOR DESIG				Protocol (optional):	: \Box LonWorks [®]					
HP: 3 Enclosure:	крм: 3500 Frame size: e: Volts: 208 Freq: 60 Hz		Enclosure: Indoor – UL TYPE 12 Outdoor – UL TYPE 4X							
Phase: 3 Efficiency: NEMA premium			L		Weather Shield □ Outdoor - UL TYPE 4X less Weather Shield					
				Disconnect switch:	: 🗆 Non-fused					
	IMP OPERATIN	IG CONDITIC	NS	ЕМІ/RFI control:	: 1-phase ivs102 unit: the вм61800-3 dire					
ANSI 125 175 psig at 150°F (100 psig at 300°F	-			Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**					
ANSI 250				Cooling:	: Fan-cooled through back channel					
375 psig at 150°F 260 psig at 300°F	(26 bars at 65°c) (21 bars at 150°c)			Ambient temperature:	: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)					
	0.125" (±3 mm) sho		or	Analog ı/o:	: Two current or voltage inputs, one current output					
 For exact installation, data please write factory for certified dimensions 				Digital ı∕o:	 Six programmable inputs (two ca be configured as outputs) 					
				Pulse inputs:	: Two programmable	9				
MECHANICAL	SEAL DESIGN	DATA		Relay outputs:	Two programmable					
See file no. 43.50	for standard mec	hanical seal de	tails as	Communication port: 1-RS485, 1-USB						
indicated below				*If minimum maintained system pressure is not known: Default to 40% of design head						

guaranty performance to any system wide harmonic specification or the costs to

Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic

meet a system wide specification. If supplied with the system electrical details,


mitigation and the costs for such mitigation.

Armstrong seal reference number

□ A1 (c) □ Others: _____

SUBMITTAL 1506-003.0 Design Envelope 4300 VIL Single phase

2




D	I	Μ	Ε	Ν	S	I	0	Ν	D	Α	T,	Α	

•••••••••••••••••••

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	145	182
Size:	1.5×1.5×6	1.5×1.5×6
HP:	3	3
RPM:	3500	3500
AB:	28.82(732)	35.23(895)
в:	4.53(115)	4.53(115)
с:	4.53(115)	4.53(115)
D:	7.25(184)	7.25(184)
E:	13.71(348)	17.90(455)
F:	13.71(348)	17.90(455)
P:	8.63(219)	9.56(243)
s:	7.00(178)	7.00(178)
SD:	14.25(362)	14.25(362)
т:	4.25(108)	4.25(108)
XY:	22.00(559)	26.39(670)
Weight:	205(93.0)	-

Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI


+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

Dimensions – inch (mm) Weight – Ibs (kg)

:



в