

# DESIGN ENVELOPE 4300 VIL 1615L350.0 SUBMITTAL

File No: 101.5191 Date: MARCH 24, 2017 Supersedes: 100.4214 Date: DECEMBER 17, 2015

Representative:	
Order No:	Date:
Submitted by:	Date:
Approved by:	Date:
CONTROLS DATA	
Orientatio	n: ☐ L1 (default) ☐ L2 ☐ L3 ☐ L4
	): □ BACNet <sup>™</sup> MS/TP □ BACNet <sup>™</sup> TCP/IP □ Modbus RTU
•	e: 🗆 Indoor – UL TYPE 12
Fused disconnect switc	<b>h:</b> N/A
EMI/RFI contro	ol: Integrated filter designed to meet EN61800-3
	n: Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
Coolin	g: Fan-cooled through back channel
Ambient temperatur	e: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
Analog ı/	o: Two current or voltage inputs, one current output
Digital ı/	o: Six programmable inputs (two can be configured as outputs)
Pulse input	s: Two programmable
Relay output	s: Two programmable
Communication por	<b>t:</b> 1-RS485, 1-USB
guaranty performance to any syst to meet a system wide specificati Armstrong will run a computer si system harmonic levels are excee	c drive via built-in DC line reactors. This does not sem wide harmonic specification or the costs on. If supplied with the system electrical details, mulation of the system wide harmonics. If ded Armstrong can also recommend additional is for such mitigation.
t	Order No:

See file no. 43.50 for standard mechanical seal details as

indicated below

☐ c1 (a)

Armstrong seal reference number

☐ Others: \_

ctors. This does not ion or the costs m electrical details, armonics. If mmend additional

2

# **OPTIONS**

## SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

# □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

# ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

# ☐ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

## Cooling

Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	

## **OPTIONAL SERVICES**

## ON-SITE PUMP COMMISSIONING



#### **PUMP MANAGER**



Online service for sustained pump performance and enhanced reliability.


Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Only available if sensorless bundle is enabled

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

#### **DIMENSION DATA**

#### INDOOR (UL TYPE 12/ODP)

**Size:** 16×16×15L

**HP:** 350 **RPM:** 1780

**AB:** 65.30(1659)

**B:** 20.30(516)

**c:** 15.30(389)

**D:** 36.00(914)

**D.** 50.00(714)

**E:** 25.05(636)

**P:** 22.44(570)

**F:** 25.05(636)

**s:** 29.00(737) **sp:** 65.00(1651)


**T:** 17.60(447)


**XY:** 65.26(1658)

Weight: 5220(2367.8)


Dimensions - inch (mm) Weight - lbs (kg)

## INDOOR





## **CONTROL ORIENTATIONS**



#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

#### BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (O) 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

## BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

## SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP FENG XIAN DISTRICT, SHANGHAI P.R.C. 201401 +86 21 3756 6696

# SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

