

DESIGN ENVELOPE 4300 VIL

SINGLE PHASE | 0206-002.0 | SUBMITTAL

File No: 100.4267

Date: OCTOBER 27, 2014


Supersedes: NEW

Date: NEW

Job:			Repre	sentative:		
			Order	No:	Date:	
Engineer:			Subm	itted by:	Date:	
			Appro	oved by:	Date:	
PUMP DESIG	N DATA			CONTROLS DATA		
	USgpm (L/s)			Power supply:	Volts: 200-240VAC Freq: 50/60Hz Phase: 1	
	озуртт (L/s/			Sensorless Control:		
Temperature:	°F (°C)	Specific gravity	:	Minimum system pressure to be maintained:	ft (m)*	
Suction: 2" (50mm) Discharge: 2" (50mm)			(50mm)	Orientation:	□ L1 (default) □ L2 □ L3 □ L4	
				Protocol (standard):	☐ Modbus rtu ☐ BACnet™ MS/TF☐ Johnson® N2 ☐ Siemens® FLN	
MOTOR DESIGN DATA				Protocol (optional):	\square LonWorks $^{\circledR}$	
	крм: 2900 Volts: 208			Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with Weather Shield	
Phase: 3	Efficiency: N	ficiency: NEMA premium			☐ Outdoor - UL TYPE 4X less Weather Shield	
				Disconnect switch:	\square Non-fused	
MAXIMUM PUMP OPERATING CONDITIONS				ЕМІ∕RFI control:	1-phase IVS102 units do not meet the EN61800-3 directive	
ANSI 125 175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C)				Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**	
ANSI 250				Cooling:	Fan-cooled through back channel	
375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C)				Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)	
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for 				Analog ı/o:	Two current or voltage inputs, one current output	
certified dimensions				Digital ı/o:	Six programmable inputs (two can be configured as outputs)	
				Pulse inputs:	Two programmable	
MECHANICAL	L SEAL DESIGN	DATA		Relay outputs:	Two programmable	
See file no. 43.50 for standard mechanical seal details as				Communication port:	1-RS485, 1-USB	
indicated below				*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not		
Armstrong seal reference number				guaranty performance to any system wide harmonic specification or the costs to		
☐ A1 (c) ☐ Others:				meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system		

harmonic levels are exceeded Armstrong can also recommend additional harmonic

 $\label{eq:mitigation} \mbox{mitigation and the costs for such mitigation.}$





Performance curves are for reference only. $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$


DIMENSION DATA


	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	143	143
Size:	2×2×6	2×2×6
HP:	2	2
RPM:	2900	2900
AB:	28.85(733)	34.88(886)
в:	4.63(118)	4.63(118)
c:	4.50(114)	4.50(114)
D:	7.00(178)	7.00(178)
E:	13.71(348)	17.19(437)
F:	13.71(348)	17.19(437)
P:	8.63(219)	7.28(185)
s:	8.00(203)	8.00(203)
SD:	15.00(381)	15.00(381)
T:	4.88(124)	4.88(124)
XY:	22.03(560)	20.53(521)
Weight:	194(88.0)	203(92.1)


Dimensions - inch (mm) Weight - lbs (kg)














TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM