

# **DESIGN ENVELOPE EXPRESS PUMP** 4300 |

1508-001.0 | SUBMITTAL

File No: 100.3012

Date: DECEMBER 24, 2015

Supersedes: 100.3012

Date: SEPTEMBER 22, 2015

Job:	F	Representative:	
	(	Order No:	Date:
Engineer:		submitted by:	Date:
Contractor:	<i>F</i>	Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	<b>∕</b> ⇒EXPRESS
No. of pumps:	Tag:	Sensorless Control:	Standard <b>TV LANE</b>
Capacity:USgpm (L/s) Liquid:			ft (m)*
Temperature: °F (°C)	Specific gravity:	Orientation:	L1
Suction: 1.5" (38mm)	Discharge: 1.5" (38mm	) Protocol:	BACnet <sup>™</sup>
OSHPD Seismic Certification OSP-	0422-10	Enclosure:	Indoor - UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MOTOR DESIGN DATA  HP:1 RPM:1800 Frame size:	143 Enclosure: TEFC	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
Volts: ☐ 230V ☐ 460V ☐ 575V	,5	Cooling:	Fan-cooled through back channel
Phase: 3 Efficiency: NEMA prem		Ambient temperature:	: -10°c to +45°c up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS		Analog ı/o:	Two current or voltage inputs, one current output
ANSI 125 175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	: Two programmable
ANSI 250		Relay outputs:	: Two programmable
375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C)		Communication port:	: 1-RS485, 1-USB
		* If minimum maintained system press	sure is not known: Default to 40% of design head

\*\*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

MECHANICAL SEAL DESIGN DATA

certified dimensions


• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$ 



# TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

## MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

### **DIMENSION DATA**

	INDOOR (UL TYPE 12/TEFC)		
	(02 1112 12) 121 0)		
Frame size:	143		
Size:	1.5×1.5×8		
HP:	1		
RPM:	1800		
AB:	24.92(633)		
В:	5.80(147)		
c:	5.80(147)		
D:	8.00(203)		
E:	11.85(301)		
P:	8.63(219)		
F:	19.85(504)		
s:	8.00(203)		
SD:	16.00(406)		
T:	4.59(117)		

**XY:** 22.03(560)

**Weight:** 208(94.3)

Dimensions - inch (mm) Weight - lbs (kg)

