

DESIGN ENVELOPE EXPRESS PUMP 4300 |

0810-040.0 | SUBMITTAL

File No: 100.3056

Date: DECEMBER 24, 2015

Supersedes: 100.3056

Date: SEPTEMBER 22, 2015

Job:	Representative:	
	Order No:	Date:
Engineer:	Submitted by:	Date:
Contractor:	Approved by:	Date:
PUMP DESIGN DATA	CONTROLS DATA	/ ⇒EXPRESS
No. of pumps: Tag:	Sensorless Control: St	tandard TV LANE
Capacity:USgpm (L/s) Head:ft Liquid: Viscosity:	· · · · · · · · · · · · · · · · · · ·	ft (m)*
Temperature: °F (°C) Specific gravity:	•	
Suction: 8" (200mm) Discharge: 8" (200m	m) Protocol: BA	Acnet [™]
OSHPD Seismic Certification OSP-0422-10	Enclosure: In	ndoor – UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		ntegrated filter designed to meet N61800-3
MOTOR DESIGN DATA HP: 40 RPM: 1800 Frame size: 324 Enclosure: ODP	AC	ual DC-link reactors (Equivalent: 5% c line reactor) Supporting IEEE 19-1992 requirements**
Volts: ☐ 460V ☐ 575V Hertz: 60 Hz	Cooling: Fa	an-cooled through back channel
Phase: 3 Efficiency: NEMA premium 12.12	Ambient temperature: -1	o°c to +45°c up to 1000 meters above ea level (-14°F to +113°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS		wo current or voltage inputs, ne current output
ANSI 125 175 psig at 150°F (12 bars at 65°C)		ix programmable inputs (two can e configured as outputs)
100 psig at 300°F (7 bars at 150°C)	Pulse inputs: T	wo programmable

*If minimum maintained system pressure is not known: Default to 40% of design head

**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

Relay outputs: Two programmable

Communication port: 1-RS485, 1-USB

MECHANICAL SEAL DESIGN DATA

• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for

375 psig at 150°F (26 bars at 65°C)

260 psig at 300°F (21 bars at 150°C)


certified dimensions

ANSI 250

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

DIMENSION DATA

INDOOR (UL TYPE 12/ODP)

Frame size: 324

Size: 8×8×10

HP: 40 **RPM:** 1800

AB: 44.04(1119)

B: 11.56(294)

c: 8.94(227)

D: 17.00(432)

E: 16.39(416)

P: 14.13(359)

F: 43.16(1096)

s: 22.00(559)

sp: 39.00(991)

T: 9.75(248)

XY: 44.23(1123)

Weight: 1175(533.0)

Dimensions - inch (mm) Weight - lbs (kg)

