

DESIGN ENVELOPE EXPRESS PUMP 4300 |

0308-007.5 | SUBMITTAL

File No: 100.3038

Date: DECEMBER 24, 2015

Supersedes: 100.3038

Date: SEPTEMBER 22, 2015

Job: R		Representative:	
	Order	No:	Date:
Engineer: S		itted by:	Date:
Contractor:		oved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	/ ⇒EXPRESS
No. of pumps: Tag:		: Sensorless Control:	Standard LANE
Capacity:USgpm (L/s) Head: Liquid: Viscosity: _		Minimum system pressure to be maintained:	ft (m)*
Temperature: °F (°C) Specific gra	avity:	Orientation:	L1
Suction: 3" (75mm) Discharge:	3" (75mm)	Protocol:	$BACnet^{TM}$
OSHPD Seismic Certification OSP-0422-10		Enclosure:	Indoor - UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		ЕМІ/RFI control:	Integrated filter designed to meet EN61800-3
MOTOR DESIGN DATA HP: 7.5 RPM: 1800 Frame size: 213 Enclosure: TEFC		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
Volts: □ 230V □ 460V □ 575V Hertz: 60 Hz		Cooling:	Fan-cooled through back channel
Phase: 3 Efficiency: NEMA premium 12.12		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS ANSI 125 175 psig at 150°F (12 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
175 psig at 150 F (12 bars at 05 C) 100 psig at 300°F (7 bars at 150°C)		Pulse inputs:	Two programmable
ANSI 250		Relay outputs:	Two programmable
375 psig at 150°F (26 bars at 65°C)		Communication port:	1-RS485, 1-USB

*If minimum maintained system pressure is not known: Default to 40% of design head

**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

MECHANICAL SEAL DESIGN DATA

• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for


260 psig at 300°F (21 bars at 150°C)

certified dimensions

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

DIMENSION DATA

INDOOR (UL TYPE 12/TEFC)

Frame size: 213 **Size:** 3×3×8

> **HP:** 7.5 **RPM:** 1800

AB: 31.74(806)

B: 6.75(171)

c: 5.80(147)

D: 10.00(254)

E: 14.73(374)

P: 12.13(308)

F: 26.73(679)

s: 12.00(305)

sp: 22.00(559) **T:** 6.31(160)

XY: 28.04(712)

Weight: 326(147.9)

Dimensions - inch (mm) Weight - lbs (kg)

