

# DESIGN ENVELOPE 4300 VIL 0611-010.0 SUBMITTAL

FLOW READOUT ACCURACY

±5% accuracy.

The Design Envelope model selected will provide flow

reading on the controls local keypad & digitally for the

BMS. The model readout will be factory tested to ensure

File No: 101.5187

Date: AUGUST 1, 2018

Supersedes: 101.5095

Date: MARCH 30, 2018

Job:	Representa	Representative:		
	Order No: _		Date:	
Engineer:	Submitted	by:	Date:	
Contractor:	Approved b	py:	Date:	
PUMP DESIGN DATA	co	ONTROLS DATA		
No. of pumps: Tag:		Orientation:	☐ L1 (default) ☐ L2 ☐ L3 ☐ L4	
Capacity:USgpm (L/s) Head: _ Liquid: Viscosi Temperature: °F (°C) Specific	ty:	Protocol (standard):	<ul> <li>□ BACnet™ MS/TP</li> <li>□ BACnet™ TCP/IP</li> <li>□ Modbus RTU</li> </ul>	
	rge: 6" (150mm)	Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with Weather Shield ☐ Outdoor – UL TYPE 4X less Weather Shield	
MOTOR DESIGN DATA	Fr	used disconnect switch:		
HP: RPM: Frame size: Volts: Hertz: 60 Hz Pha	•	емі/RFI control:	Integrated filter designed to meet EN61800-3	
Efficiency: NEMA premium 12.12  MAXIMUM PUMP OPERATING CON		Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**	
ANSI 125 - (CONSTRUCTION: BF)		Cooling:	Fan-cooled through back channel	
175 psig at 150°F (12 bar at 65°C) 100 psig at 300°F (7 bar at 150°C)			-10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)	
<b>ANSI 250 - (CONSTRUCTION: DBF)</b> 375 psig at 150°F (26 bar at 65°C)  260 psig at 300°F (21 bar at 150°C)		Analog ı/o:	Two current or voltage inputs, one speed output	
200 psig at 500 1 (2) but at 150 c/		Digital ı/o:	Two inputs, two outputs	
MECHANICAL SEAL DESIGN DATA		Pulse inputs:	Two programmable	
See file no. 43.50 for standard mechanical indicated below  Armstrong seal reference number		Relay outputs: Communication port:	Two programmable 1-RS485	
	•			

<sup>\*\*</sup>The IVS drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

2

# **OPTIONS**

## SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

# □ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

### ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

\*Only available if sensorless bundle is enabled

#### □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

\*Only available if sensorless bundle is enabled

# □ ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

# □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Cooling

Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

## **OPTIONAL SERVICES**

## **ON-SITE PUMP COMMISSIONING**



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

#### PUMP MANAGER




As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.

Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

\*The Service requires an active internet connection.


3




Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.


## INDOOR





# OUTDOOR






## **DIMENSION DATA**

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
		(
Frame size:	215	215
Size:	6×6×11.5	6×6×11.5
HP:	10	10
RPM:	1500	1500
AB:	28.42(722)	28.42(722)
B:	9.80(249)	9.80(249)
C:	8.50(216)	8.50(216)
D:	16.50(419)	16.50(419)
E:	13.17(335)	13.17(335)
F:	13.17(335)	13.17(335)
P:	12.13(308)	11.25(286)
s:	18.50(470)	18.50(470)
SD:	35.00(889)	35.00(889)
T:	9.75(248)	9.75(248)
XY:	28.16(715)	29.28(744)
Weight:	626(283.9)	668(303.0)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

## **CONTROL ORIENTATIONS**



#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

#### BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

## MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

#### SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD. HONGKOU DISTRICT, SHANGHAI CHINA 200085 +86 (0) 21 5237 0909

### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

