

DESIGN ENVELOPE 4300 VIL 0611-040.0 SUBMITTAL

File No: 101.5197 Date: AUGUST 1, 2018 Supersedes: 101.5103 Date: MARCH 30, 2018

Jop:	Representative:		
	Order No:	_Date:	
Engineer:	Submitted by:	_Date:	
Contractor:	Approved by:	_ Date:	

PUMP DESIGN DATA CONTROLS DATA No. of pumps: _____ Tag: _____ **Orientation:** \Box L1 (default) \Box L2 \Box L3 \Box L4 Capacity: _____USqpm (L/s) Head: _____ft (m) **Protocol (standard):** □ BACnet[™] MS/TP ___ Viscosity: ____ Liquid: □ BACNET[™] TCP/IP Temperature: ______ °F (°C) Specific gravity: _____ □ Modbus rtu **Enclosure:** Indoor – UL TYPE 12 Suction: 6" (150mm) Discharge: 6" (150mm) □ Outdoor – UL TYPE 4X with **OSHPD** Seismic Certification OSP-0422-10 Weather Shield UL STD 778 & CSA STD C22.2 NO.108 certified □ Outdoor – UL TYPE 4X less Test report is supplied with each pump Weather Shield MOTOR DESIGN DATA Fused disconnect switch: нр: _____ RPM: _____ Frame size: _____ Enclosure: ____ **EMI/RFI control:** Integrated filter designed to meet Volts: Hertz: 60 Hz Phase: 3 EN61800-3 Efficiency: NEMA premium 12.12 Harmonic suppression: Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE MAXIMUM PUMP OPERATING CONDITIONS 519-1992 requirements** ANSI 125 - (CONSTRUCTION: BF) **Cooling:** Fan-cooled through back channel 175 psig at 150°F (12 bar at 65°C) Ambient temperature: -10°C to +45°C up to 1000 meters 100 psig at 300°F (7 bar at 150°C) above sea level (+14°F to +113°F, 3300 ft) ANSI 250 - (CONSTRUCTION: DBF) Analog I/O: Two current or voltage inputs, 375 psig at 150°F (26 bar at 65°C) one speed output 260 psig at 300°F (21 bar at 150°C) Digital I/O: Two inputs, two outputs MECHANICAL SEAL DESIGN DATA Pulse inputs: Two programmable Relay outputs: Two programmable

See file no. 43.50 for standard mechanical seal details as indicated below Armstrong seal reference number

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure $\pm 5\%$ accuracy.

**The IVS drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

Communication port: 1-RS485

Design Envelope 4300 VIL

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained

ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

П **ENERGY PERFORMANCE BUNDLE**



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

*Only available if sensorless bundle is enabled

PROTECTION BUNDLE




Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- · Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

gpm (L/s) Minimum flow rate





*Only available if sensorless bundle is enabled

п ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

• 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

DUAL SEASON SETUP п



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point gpm (L/s) at ft (m) Minimum system pressure to be maintained ft (m)

Heating

Duty point	gpm (L/s) at	ft (m)		
Minimum system pressure to be maintained				
f	t (m)			

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

PUMP MANAGER



As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.


Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

*The Service requires an active internet connection.



Design Envelope 4300 VIL








Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.


INDOOR











DIMENSION DATA


	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	324	324
Size:	6×6×11.5	6×6×11.5
HP:	40	40
RPM:	1800	1800
AB:	43.68(1110)	49.08(1247)
в:	9.88(251)	9.88(251)
c:	8.64(219)	8.64(219)
D:	16.50(419)	16.50(419)
E:	37.69(957)	41.92(1065)
F:	37.69(957)	41.92(1065)
P:	14.13(359)	17.00(432)
s:	18.50(470)	18.50(470)
SD:	35.00(889)	35.00(889)
т:	9.75(248)	9.75(248)
XY:	43.88(1114)	44.47(1130)
Weight:	1110(503.5)	1175(533.0)

Dimensions - inch (mm)

• Weight – Ibs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

CONTROL ORIENTATIONS



TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

MANCHESTER

wolverton street manchester united kingdom m11 2et +44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. hongkou district, shanghai china 200085 +86 (0) 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

ENERGA SENSE SENSE