

# DESIGN ENVELOPE 4302 DUALARM | 0608-010.0 |


**Date:** JAN. 16, 2015 Supersedes: 100.4464 Date: OCTOBER 30, 2015

SUBMITTAL

Job:	Representative:				
	Order No:		Date:		
Engineer:	Submitted by:	ubmitted by:		Date:	
Contractor:	Approved by:		Date:		
PUMP DESIGN DATA	CONTROLS	DATA			
No. of pumps: Tag:	Senso	orless Control:	Standard		
Capacity:USgpm (L/s) Head:f           Liquid:Viscosity:	اما	stem pressure be maintained:		ft (m)*	
Temperature:°F (°C) Specific gravity:		col (standard):	☐ Modbus RTU☐ Johnson® N2	☐ BACnet™ MS/TP☐ Siemens® FLN	
Suction: 6" (150mm) Discharge: 6" (150mi	n) Proto	col (optional):	☐ LonWorks®	_ 0.60	
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		•		☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4x with Weather Shield	
MOTOR DESIGN DATA			☐ Outdoor - UL		
нр: RPM: Frame size: Enclosure:	Fused disc	onnect switch:			
Volts: Hertz: 60 Hz Phase: 3		Duty/standby			
Efficiency: NEMA premium 12.12	:	pre-wired bridge: ☐  EMI/RFI control: Integrated filter designed to me EN61800-3  Harmonic suppression: Dual DC-link reactors (Equivale AC line reactor) Supporting IEEE 519-1992 requirements**		designed to meet	
MAXIMUM PUMP OPERATING CONDITIONS  ANSI 125	Harmoni			ual DC-link reactors (Equivalent: 5% line reactor) Supporting IEEE	
175 psig at 150°F (12 bars at 65°C)		Cooling:	: Fan-cooled through back channel		
140 psig at 250°F (10 bars at 121°C) ANSI <b>250</b>	Ambien	t temperature:	-10°C to +45°C up sea level (-14°F t	o to 1000 meters above to +113°F, 3300 ft)	
250 psig at 150°F (17 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)		Analog ı/o:	Two current or v		
• Tolerance of ±0.125" (±3 mm) should be used		Digital ı/o:	Six programmat be configured as	ole inputs (two can s outputs)	
<ul> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		Pulse inputs:	Two programma	able	
certified difficultions	:	Relay outputs:	Two programma	able	
MECHANICAL SEAL DESIGN DATA	Commi	unication port:	1-RS485, 1-USB		
See file no. 43.50 for standard mechanical seal details as indicated below	**The IVS 102 driv	*If minimum maintained system pressure is not known: Default to 40% of design head  **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet			
Armstrong seal reference number	a system wide s	specification. If supp	lied with the system el	ectrical details, Armstrong	
□ c1 (a) □ Others:	•	will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation			

and the costs for such mitigation.

2



Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$ 

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

#### **DIMENSION DATA**

	INDOOR	OUTDOOR	
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)	
Frame size:	215	215	
Size:	6×6×8	6×6×8	
HP:	10	10	
RPM:	1800	1800	
AB:	31.89(810)	37.68(957)	
B1:	9.75(248)	9.75(248)	
B2:	9.75(248)	9.75(248)	
C1:	16.90(429)	16.90(429)	
C2:	17.59(447)	17.59(447)	
D1:	16.75(425)	16.75(425)	
D2:	16.75(425)	16.75(425)	
E:	7.59(193)	8.25(210)	
P:	12.13(308)	11.25(286)	
F:	16.73(425)	20.25(514)	
SD:	33.88(860)	33.88(860)	
T:	7.875(200)	7.875(200)	
XY:	28.19(716)	29.32(745)	
Weight:	872(395.5)	956(433.6)	

OUTDOOR

Dimensions - inch (mm) Weight - lbs (kg)

## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER


+44 (0) 8444 145 145

## BANGALORE


+91 (0) 80 4906 3555


# SHANGHAI

+86 21 3756 6696



INDOOR





 ${\tt ARMSTRONGFLUIDTECHNOLOGY.COM}$