

# **DESIGN ENVELOPE** 4302 DUALARM

0810-007.5 | SUBMITTAL

File No: 104.5061

Date: DECEMBER 16, 2020

Supersedes: 104.5061

Date: JULY 8, 2019

Job:		Re	Representative:		
		0	rder No:	Date:	
Engineer:		Sı	ubmitted by:	Date:	
Contractor: Appro			pproved by:	Date:	
PUMP DESIG	IN DATA		CONTRO	LS DATA	
No. of pumps:_		Tag:	_ :	Protocol (standard): ☐ BACnet™ MS/TP	
		USgpm(L/s	:	☐ BACnet™ TCP/IP	
	_	Capacity split	:	☐ Modbus RTU	
		USgpm(L/s	•	Enclosure: ☐ Indoor - UL TYPE 12	
		USgpm(L/s	•	☐ Outdoor – UL TYPE 4X with	
			•	Weather Shield	
		Viscosity:	:	☐ Outdoor - UL TYPE 4X less Weather Shield	
		Specific gravity:		sed disconnect switch:	
Suction: 8" (20	omm)	Discharge: 8" (200mm)		EMI/RFI control: Integrated filter designed to	
оѕнро Seismic		-		meet EN61800-3	
UL STD 778 & CS			н	larmonic suppression: Dual DC-link reactors	
Test report is su	applied with eac	h pump		(Equivalent: 5% Ac line reactor	
MOTOR DESI	IGN DATA			Supporting IEEE 519-1992 requirements**	
		Frame size:	-	Cooling: Fan-cooled through back channel	
		Hertz: 60 Hz : NEMA premium 12.12	,	Ambient temperature: -10°c to +45°c up to 1000 mete above sea level (+14°F to +113° 3300 ft)	
MAXIMUM P	UMP OPERA	TING CONDITIONS		Analog I/o: Two current or voltage inputs,	
ANSI 125 - (C	ONSTRUCTION	: BF)		one speed output	
175 psig at 150°F				Digital I/o: Two inputs, two outputs	
140 psig at 250°	_			Pulse inputs: Two programmable	
-4- berg2	. (	-,		Relay outputs: Two programmable	
				Communication port: 1-RS485	
MECHANICA See file no. 43.5 indicated below Armstrong seal	50 for standard i	mechanical seal details as	guaranty pei meet a syste Armstrong v system harm	** The IVS drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.	
□ c1 (a) □	Others:		: FLOW R	READOUT ACCURACY	

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure  $\pm 5\%$  accuracy.

2

# **OPTIONS**

## SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## □ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

# □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

• Minimum flow control - Attempts to maintain flow rate to pre-set minimum to protect

equipment in system

• Bypass valve control - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

# ☐ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

## Cooling

Duty point	gpm (L/s) at	ft (m)					
Minimum system pressure to be maintainedft (m)							
Heating							
Duty point	gpm (L/s) at	ft (m)					
Minimum sys	tem pressure to b	be maintained					

# **OPTIONAL SERVICES**

#### ON-SITE PUMP COMMISSIONING



## **PUMP MANAGER**



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)


<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

<sup>\*</sup>Only available if sensorless bundle is enabled


<sup>\*</sup>Available in single pump operation only

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



## **DIMENSION DATA**

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	254	254
Size:	8×8×10	8×8×10
HP:	7.5	7.5
RPM:	1800	1800
AB:	31.49(800)	31.49(800)
B1:	12.00(305)	12.00(305)
B2:	11.50(292)	11.50(292)
C1:	20.56(522)	20.56(522)
C2:	21.00(533)	21.00(533)
D1:	21.00(533)	21.00(533)
D2:	25.00(635)	25.00(635)
E:	8.90(226)	8.90(226)
F:	17.95(456)	17.95(456)
P:	13.38(340)	13.38(340)
SD:	46.00(1168)	46.00(1168)
т:	8.86(225)	8.86(225)
XY:	34.20(869)	34.20(869)
Weight:	1635(741.6)	1717(778.7)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

## BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM, B62 8DJ +44 8444 145 145

## MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

# SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

#### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

### MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934