

DESIGN ENVELOPE 4302 DUALARM | 0608-050.0 | submittal

File No: 100.4478 Date: OCTOBER 30, 2015 Supersedes: NEW Date: NEW

Job:	Repres	sentative:	
	Order	No:	Date:
Engineer: Subm		tted by:	Date:
Contractor: Appro		ved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps: Tag:		Sensorless Control:	Standard
Capacity:USgpm (L/s) Head: Liquid: Viscosity:		Minimum system pressure to be maintained:	ft (m)*
Temperature:°F (°C) Specific g		Protocol (standard):	□ Modbus rtu □ bacnet [™] ms/tp □ Johnson® N2 □ Siemens® fln
Suction: 6" (150mm) Discharge: 6" (150mm)		Protocol (optional):	
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		Enclosure:	□ Indoor – UL TYPE 12 □ Outdoor – UL TYPE 4x with Weather Shield □ Outdoor – UL TYPE 4x less
MOTOR DESIGN DATA HP: RPM: Frame size: Er	iclosure:	Fused disconnect switch:	Weather Shield
Volts: Hertz: 60 Hz Phas		Duty/standby	
Efficiency: NEMA premium 12.12		pre-wired bridge: ЕМІ/RFI control:	L Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATING COND Ansi 125	ITIONS	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Cooling:	Fan-cooled through back channel
ANSI 250		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
250 psig at 150°F (17 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)		Analog ı/o:	Two current or voltage inputs, one current output
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB
See file no. 43.50 for standard mechanical seal details as		*If minimum maintained system press	sure is not known: Default to 40% of design head

:

indicated below


🗆 c1 (a)

Armstrong seal reference number

□ Others: _

*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.





 Frame size:
 324
 324

 Size:
 6×6×8
 6×6×8

 HP:
 50
 50

INDOOR

OUTDOOR

(UL TYPE 12/ODP) (UL TYPE 4X/TEFC)

DIMENSION DATA


·		
HP:	50	50
RPM:	1500	1500
AB:	46.82(1189)	46.82(1189)
B1:	9.75(248)	9.75(248)
B2:	9.75(248)	9.75(248)
C1:	16.90(429)	16.90(429)
C2:	17.63(448)	17.63(448)
D1:	16.81(427)	16.81(427)
D2:	16.81(427)	16.81(427)
E:	13.91(353)	13.91(353)
F:	22.68(576)	22.68(576)
P:	17.00(432)	17.00(432)
SD:	33.94(862)	33.94(862)
т:	7.88(200)	7.88(200)
XY:	44.45(1129)	44.45(1129)
Weight:	1151(522.1)	1209(548.2)


Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.


Dimensions - inch (mm)


Weight – Ibs (kg)

:









TORONTO

+1 416 755 2291

BUFFALO +1 716 693 8813

BIRMINGHAM +44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

+86 21 3756 6696