

DESIGN ENVELOPE 4312 TWIN | 0206-005.0 | SUBMITTAL

File No: 100.4708

Date: JANUARY 14, 2016

Supersedes: 100.4708

Date: AUGUST 14, 2015

Job:		Representative:	
		Order No:	Date:
Engineer: Sul Contractor: Ap		Submitted by:	Date:
		Approved by:	Date:
PUMP DESIGN DATA		: CONTROLS DATA	
No. of pumps:	Tag:	: Sensorless Control:	Standard
Capacity:USgpm (L/s)	Head:ft (m	Minimum system pressure	ft (m)*
Temperature:°F (°C)	Specific gravity:	5 1 14 1 15	☐ Modbus RTU ☐ BACnet TM MS/TP☐ Johnson® N2 ☐ Siemens® FLN
-	Discharge: 2" (50mm)	Protocol (optional):	□ LonWorks®
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with Weather Shield ☐ Outdoor - UL TYPE 4X less
MOTOR DESIGN DATA		Fused disconnect switch:	Weather Shield
HP: RPM: Frame si		Duty/standby pre-wired bridge:	П
Volts: Hertz: 60 Hz Phase: 3			Integrated filter designed to meet
Efficiency: NEMA premium 12.12		EWII/ RFI CONCIOI.	EN61800-3
MAXIMUM PUMP OPERA	TING CONDITIONS	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125		Cooling:	Fan-cooled through back channel
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Ambient temperature:	-10°c to +45°c up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	Two programmable
MECHANICAL CEAL DECICE DATA		Relay outputs:	Two programmable
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB
See file no. 43.50 for standard mechanical seal details as indicated below		•	sure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not
Armstrong seal reference number		guaranty performance to any syste	m wide harmonic specification or the costs to meet


☐ c1 (a)

☐ Others: _

^{*}If minimum maintained system pressure is not known: Default to 40% of design head

**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.


ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

DIMENSION DATA

	INDOOD	OUTDOOD
	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
		· · · · · · · · · · · · · · · · · · ·
Frame size:	182TC	184TC
Size:	2×2×6	2×2×6
HP:	5	5
RPM:	3000	3000
AB:	26.65(677)	32.61(828)
В1:	7.87(200)	7.87(200)
B2:	7.87(200)	7.87(200)
C1:	12.34(314)	12.34(314)
C2:	12.34(314)	12.34(314)
D1:	7.28(185)	7.28(185)
D2:	7.28(185)	7.28(185)
E:	6.84(174)	7.50(191)
F:	13.58(345)	19.50(495)
P:	10.38(264)	9.56(243)
SD:	12.99(330)	12.99(330)
T:	5.30(135)	5.30(135)
XY:	26.56(674)	26.44(671)
Weight:	406(184.2)	520(235.9)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

