

DESIGN ENVELOPE 4312 TWIN | 0406-001.5 | SUBMITTAL

File No: 100.4728

Date: JANUARY 14, 2016

Supersedes: 100.4728

Date: AUGUST 14, 2015

Job:		Representative:	
		Order No:	Date:
Engineer: Sul Contractor: Ap		Submitted by:	Date:
		Approved by:	Date:
PUMP DESIGN DATA		: CONTROLS DATA	
No. of pumps:	Tag:	: Sensorless Control:	Standard
Capacity:USgpm (L/s)	Head:ft (m	Minimum system pressure	ft (m)*
Temperature:°F (°C)	Specific gravity:	B (14 (1 1)	☐ Modbus RTU ☐ BACnet TM MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 4" (100mm)		Protocol (optional):	□ LonWorks®
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with Weather Shield
MOTOR DESIGN DATA		Fused disconnect switch:	☐ Outdoor - UL TYPE 4x less Weather Shield ☐
HP: RPM: Frame si		Duty/standby pre-wired bridge:	П
Volts: Hertz: 60 Hz Phase: 3			
Efficiency: NEMA premium 12.1	2	EMI/ RFI CONTROL	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERA	TING CONDITIONS	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125		Cooling:	Fan-cooled through back channel
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Ambient temperature:	-10°c to +45°c up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Analog I/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	Two programmable
MECHANICAL CEAL DECICAL DATA		Relay outputs:	Two programmable
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB
See file no. 43.50 for standard mechanical seal details as indicated below		•	sure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not
Armstrong seal reference number		guaranty performance to any system	m wide harmonic specification or the costs to meet


☐ c1 (a)

☐ Others: _

If minimum maintained system pressure is not known: Default to 40% of design head

*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.





Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.


ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	145TC	145TC
Size:	4×4×6	4×4×6
HP:	1.5	1.5
RPM:	1500	1500
AB:	24.25(616)	30.21(767)
B1:	9.65(245)	9.65(245)
B2:	9.65(245)	9.65(245)
C1:	15.76(400)	15.76(400)
C2:	16.12(409)	16.12(409)
D1:	11.42(290)	11.42(290)
D2:	11.42(290)	11.42(290)
E:	4.13(105)	6.09(155)
F:	12.58(319)	18.50(470)
P:	8.63(219)	7.28(185)
SD:	19.29(490)	19.29(490)
T:	7.01(178)	7.01(178)
XY:	22.28(566)	20.78(528)
Weight:	498(225.9)	514(233.1)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145


BANGALORE


+91 (0) 80 4906 3555


SHANGHAI

+86 21 3756 6696









ARMSTRONGFLUIDTECHNOLOGY.COM