

DESIGN ENVELOPE 4302 DUALARM

0810-015.0 | SUBMITTAL

File No: 104.5063

Date: DECEMBER 16, 2020

Supersedes: 104.5063

Date: JULY 8, 2019

Job:		R	Representative:		
		(Order No:		Date:
Engineer:		S	Submitted by:		
Contractor: Ap			approved by:		
PUMP DESIG	SN DATA		CONTRO	OLS DATA	
No. of pumps:_	Т	- ag:	_ :	Protocol (standard):	: □ BACnet™ MS/TP
Total system de	esign flow:	USgpm(L/	s)		☐ BACnet™ TCP/IP
Head:	ft(m) C	Capacity split	_%		☐ Modbus RTU
Flow per pump	head:	USgpm(L/	s)	Enclosure	□ Indoor – UL TYPE 12
		USgpm(L/	•		☐ Outdoor – UL TYPE 4X with Weather Shield
		/iscosity:	:		☐ Outdoor - UL TYPE 4X less
		pecific gravity:	:		Weather Shield
Suction: 8" (20		Discharge: 8" (200mm)		sed disconnect switch:	
		J	:	EMI/RFI control:	Integrated filter designed to
	Certification OSP- SA STD C22.2 NO.	•			meet EN61800-3
	upplied with each			Harmonic suppression:	
•			:		(Equivalent: 5% AC line reactor) Supporting IEEE 519-1992
MOTOR DES	IGN DATA		:		requirements**
HD.	DDW.	Frame size:	:	Cooling	Fan-cooled through back
		Hertz: 60 Hz	- :		channel
Phase: 3		NEMA premium 12.12		Ambient temperature:	: -10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)
MAXIMUM F	OUMP OPERAT	ING CONDITIONS	:	Analog ı/o:	: Two current or voltage inputs,
ANSI 125 - (CONSTRUCTION: BF)				_	one speed output
_		·		Digital ı/o:	Two inputs, two outputs
175 psig at 150°F (12 bar at 65°C) 140 psig at 250°F (10 bar at 121°C)			:	Pulse inputs:	: Two programmable
.4. b a =2.	, (,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		:		: Two programmable
				Communication port:	, ,
MECHANICAL SEAL DESIGN DATA See file no. 43.50 for standard mechanical seal details as indicated below Armstrong seal reference number			guaranty pe meet a syst Armstrong system hari	** The IVS drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.	
□ c1 (a) □	Others:		: FLOW	READOUT ACCUR	ACY
			:		- -

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure $\pm 5\%$ accuracy.

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

□ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

• Minimum flow control - Attempts to maintain flow rate to pre-set minimum to protect

equipment in system

 Bypass valve control - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

☐ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point	gpm (L/s) at	ft (m)					
Minimum system pressure to be maintained ft (m)							
Heating							
Duty point	gpm (L/s) at	ft (m)					
Minimum system pressure to be maintained ft (m)							

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	254	254
Size:	8×8×10	8×8×10
HP:	15	15
RPM:	1800	1800
AB:	33.21(844)	39.00(991)
B1:	12.00(305)	12.00(305)
B2:	11.50(292)	11.50(292)
C1:	20.58(523)	20.58(523)
C2:	21.02(534)	21.02(534)
D1:	21.00(533)	21.00(533)
D2:	25.00(635)	25.00(635)
E:	9.94(252)	8.90(226)
P:	13.38(340)	13.38(340)
F:	18.04(458)	21.44(545)
SD:	46.00(1168)	46.00(1168)
T:	8.75(222)	8.75(222)
XY:	34.13(867)	34.20(869)
Weight:	1556(705.8)	1624(736.6)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM, B62 8DJ +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934