

DESIGN ENVELOPE 4302 DUALARM

0810-020.0 | SUBMITTAL

File No: 104.5065

Date: DECEMBER 16, 2020

Supersedes: 104.5065

Date: JULY 8, 2019

Job:	Repres	Representative:	
	Order	No:	Date:
Engineer:	Submit	tted by:	Date:
Contractor: Appro		ved by:	Date:
PUMP DESIGN DATA	:	CONTROLS DATA	
No. of pumps: Tag:		Protocol (standard)	: □ BACnet™ MS/TP
Total system design flow:		, , , , , , , , , , , , , , , , , , , ,	☐ BACnet™ TCP/IP
Head:ft(m) Capacity split _	•		☐ Modbus RTU
	•	Enclosure	: 🗆 Indoor – UL TYPE 12
Flow per pump head:	•		☐ Outdoor – UL TYPE 4X with
Parallel flow:	:		Weather Shield
Liquid: Viscosity:	:		☐ Outdoor – UL TYPE 4X less Weather Shield
Temperature:°F (°C) Specific gravity		Fused disconnect switch	
Suction: 8" (200mm) Discharge: 8" ((200mm)		: Integrated filter designed to
OSHPD Seismic Certification OSP-0422-10		Emily Kirl Control	meet EN61800-3
UL STD 778 & CSA STD C22.2 NO.108 certified		Harmonic suppression	: Dual oc-link reactors
Test report is supplied with each pump			(Equivalent: 5% AC line reactor
			Supporting IEEE 519-1992
MOTOR DESIGN DATA			requirements**
HP: RPM: Frame s	ize:	Cooling	: Fan-cooled through back channel
Enclosure: Volts: Hertz: 6	50 Hz	Ambient temperature	: -10°C to +45°C up to 1000 meter
Phase: 3 Efficiency: NEMA premium 12.12		Ambient temperature	above sea level (+14°F to +113°
			3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS		Analog ı/o	: Two current or voltage inputs,
ANSI 125 - (CONSTRUCTION: BF)			one speed output
175 psig at 150°F (12 bar at 65°C)		Digital 1/0	: Two inputs, two outputs
1/5 psig at 150°F (12 bar at 05°C) 140 psig at 250°F (10 bar at 121°C)		Pulse inputs	: Two programmable
into being an edge is the earlier of			: Two programmable
		Communication port	· -
MECHANICAL SEAL DESIGN DATA		** The IVS drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional	
See file no. 43.50 for standard mechanical seal details as indicated below			
Armstrong seal reference number		harmonic mitigation and the costs for suc	ch mitigation.
☐ c1 (a) ☐ Others:		FLOW READOUT ACCUR	ACY
		The Design Envelope model sel	ected will provide flow reading

on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure $\pm 5\%$ accuracy.

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

□ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

• Minimum flow control - Attempts to maintain flow rate to pre-set minimum to protect

equipment in system

 Bypass valve control - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point	gpm (L/s) at	ft (m)		
Minimum system pressure to be maintainedft (m)				
Heating				
Duty point	gpm (L/s) at	ft (m)		
Minimum system pressure to be maintained ft (m)				

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled


^{*}Available in single pump operation only

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
_		
Frame size:	256	256
Size:	8×8×10	8×8×10
HP:	20	20
RPM:	1800	1800
AB:	35.85(911)	41.64(1058)
B1:	12.00(305)	12.00(305)
B2:	11.50(292)	11.50(292)
C1:	20.58(523)	20.58(523)
C2:	21.02(534)	21.02(534)
D1:	21.00(533)	21.00(533)
D2:	25.00(635)	25.00(635)
E:	9.94(252)	8.90(226)
P:	13.38(340)	13.38(340)
F:	18.04(458)	21.44(545)
SD:	46.00(1168)	46.00(1168)
T:	8.75(222)	8.75(222)
XY:	34.13(867)	34.20(869)
Weight:	1642(744.8)	1690(766.6)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM, B62 8DJ +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934