

DESIGN ENVELOPE 4312 TWIN | 0208-003.0 | SUBMITTAL

File No: 100.4750

Date: JANUARY 14, 2016

Supersedes: 100.4750


Date: AUGUST 14, 2015

Job:		Representative:		
		Order No:	Date:	
Engineer: Su Contractor: Ap		Submitted by:	Date:	
		Approved by:	Date:	
PUMP DESIGN DATA		CONTROLS DATA		
No. of pumps:	Tag:	Sensorless Control:	Standard	
Capacity:USgpm (L/s) Liquid:	Head:ft (m) Minimum system pressure	ft (m)*	
Temperature:°F (°C)	Specific gravity:	5 (1/) 1 ()	☐ Modbus RTU ☐ BACnet TM MS/TP☐ Johnson® N2 ☐ Siemens® FLN	
Suction: 2" (50mm)		Protocol (optional):	□ LonWorks®	
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with	
MOTOR DESIGN DATA		Fused disconnect switch:	Weather Shield ☐ Outdoor - UL TYPE 4x less Weather Shield	
нр:	e: Enclosure:			
Volts: Hertz: 60	o Hz Phase: 3	pre-wired bridge:		
Efficiency: NEMA premium 12.12		EMI/RFI control:	Integrated filter designed to meet EN61800-3	
MAXIMUM PUMP OPERAT	ING CONDITIONS	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**	
ANSI 125		Cooling:	Fan-cooled through back channel	
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Ambient temperature:	-10°c to +45°c up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)	
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Analog ı/o:	Two current or voltage inputs, one current output	
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)	
		Pulse inputs:	Two programmable	
		Relay outputs:	Two programmable	
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB	
See file no. 43.50 for standard mechanical seal details as indicated below		•	sure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not	
Armstrong seal reference number			guaranty performance to any system wide harmonic specification or the costs to meet	

☐ c1 (a)

☐ Others: _

If minimum maintained system pressure is not known: Default to 40% of design head *The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to mee a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.




Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC
Frame size:	182TC	182TC
Size:	2×2×8	2×2×8
HP:	3	3
RPM:	1800	1800
AB:	26.63(676)	32.59(828)
B1:	8.19(208)	8.19(208)
B2:	8.66(220)	8.66(220)
C1:	13.91(353)	13.91(353)
C2:	14.38(365)	14.38(365)
D1:	8.27(210)	8.27(210)
D2:	9.06(230)	9.06(230)
E:	6.84(174)	7.50(191)
F:	13.58(345)	19.50(495)
P:	10.38(264)	9.56(243)
SD:	15.75(400)	15.75(400)
T:	5.12(130)	5.12(130)
XY:	26.54(674)	26.42(671)
Weight:	465(210.9)	545(247.2)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145


BANGALORE


+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696







ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM