

DESIGN ENVELOPE 4312 TWIN | 0408-007.5 | SUBMITTAL

File No: 100.4782 Date: JANUARY 14, 2016 Supersedes: 100.4782 Date: AUGUST 14, 2015

| Job: | Representative: | |
|-------------|-----------------|-------|
| | Order No: | Date: |
| Engineer: | Submitted by: | Date: |
| Contractor: | Approved by: | Date: |
| | | |

PUMP DESIGN DATA

| | | • |
|--------------------------------------|-----------------------|----------|
| No. of pumps: | Tag: | Sei |
| Capacity:USgpm (L/s) | Head:ft (m) | Minimums |
| Liquid: | Viscosity: | t |
| Temperature:°F (°C) | Specific gravity: | Prot |
| Suction: 4" (100mm) | Discharge: 4" (100mm) | Pro |
| OSHPD Seismic Certification O | SP-0422-10 | FIU |
| UL STD 778 & CSA STD C22.2 1 | vo.108 certified | |

MOTOR DESIGN DATA

| HP: | RPM: | Frame size: | Enclosure: |
|--------|------|--------------|------------|
| Volts: | | Hertz: 60 Hz | Phase: 3 |

Efficiency: NEMA premium 12.12

MAXIMUM PUMP OPERATING CONDITIONS

ANSI 125

175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)

• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for certified dimensions

MECHANICAL SEAL DESIGN DATA

See file no. 43.50 for standard mechanical seal details as indicated below

Armstrong seal reference number

🗌 c1 (a) □ Others:

CONTROLS DATA

nsorless Control: Standard


| Minimum system pressure to be maintained: | | ft (m)* |
|--|----------------|-----------------------------------|
| Protocol (standard): | | □ bacnet™ ms/tp □ Siemens® fln |
| Protocol (optional): | □ LonWorks® | |
| Enclosure: | 🗆 Outdoor - UL | TYPE 4X with eather Shield |
| Fused disconnect switch: | | |

| Duty/standby pre-wired bridge: | |
|-----------------------------------|--|
| EMI/RFI control: | Integrated filter designed to meet EN61800-3 |
| Harmonic suppression: | Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements** |
| Cooling: | Fan-cooled through back channel |
| Ambient temperature: | -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft) |
| Analog ı/o: | Two current or voltage inputs, one current output |
| Digital ı/o: | Six programmable inputs (two can be configured as outputs) |
| Pulse inputs: | Two programmable |
| Relay outputs: | Two programmable |

Communication port: 1-RS485, 1-USB

*If minimum maintained system pressure is not known: Default to 40% of design head ** The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.


SUBMITTAL 0408-007.5




DIMENSION DATA

| | INDOOR | OUTDOOR |
|-------------|------------------|-------------------|
| | (UL TYPE 12/ODP) | (UL TYPE 4X/TEFC) |
| Frame size: | 213TC | 213TC |
| Size: | 4×4×8 | 4×4×8 |
| HP: | 7.5 | 7.5 |
| RPM: | 1800 | 1800 |
| AB: | 32.13(816) | 37.92(963) |
| B1: | 11.42(290) | 11.42(290) |
| B2: | 11.42(290) | 11.42(290) |
| C1: | 18.85(479) | 18.85(479) |
| C2: | 18.94(481) | 18.94(481) |
| D1: | 11.18(284) | 11.18(284) |
| D2: | 11.18(284) | 11.18(284) |
| E: | 7.59(193) | 8.25(210) |
| F: | 16.66(423) | 20.25(514) |
| P: | 12.13(308) | 11.25(286) |
| SD: | 20.00(508) | 20.00(508) |
| т: | 7.99(203) | 7.99(203) |
| XY: | 28.18(716) | 29.31(744) |
| Weight: | 732(332.0) | 832(377.4) |
| | | |

Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.






Dimensions - inch (mm)

Weight – Ibs (kg)

÷



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM