

DESIGN ENVELOPE 4372 TANGO | 1.5×1.5×3 (40-80) |

___ Representative: _

1503-001.0 | SUBMITTAL

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

Supersedes: 102.5101 Date: APRIL 18, 2018

	Order No:	Date:		
Engineer:	Submitted by:	Date:		
Contractor:	Approved by:	Date:		
PUMP DESIGN DATA	DEPM MOTOR AND	O CONTROL DATA		
No. of pumps: Tag:		HP: 1		
Total system design flow:USgr	·	PM: 3600		
Head:ft(m) Capacity split		ure: TEFC		
Flow per pump head:USgr	· · · · · · · · · · · · · · · · · · ·	olts:		
	Pha	ase: 3		
Parallel flow:USgr	. Efficiel	ncy: IE5		
Liquid: Viscosity:		ion: Standard		
Temperature: °F (°C) Specific gravity:	Protocol (standa	rd): ☐ BACnet™ MS/TP ☐ BACnet™ TCP/I		
Suction: 1.5" (40 mm) Discharge: 1.5" (40 m		☐ Modbus RTU		
UL STD 778 & CSA STD C22.2 NO.108 certified	Control enclos	ure: ☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X		
Test report is supplied with each pump	: Fused disconnect swi	'		
MATERIALS OF CONSTRUCTION	•	trol: Integrated filter designed to meet EN61800-3		
□ ANSI 125 CONSTRUCTION: LPDESF		ion: Equivalent: 5% Ac line reactor - Sup- porting IEEE 519-1992 requirements**		
E-coated ductile iron A536 Gr 65-45-12, stainles ☐ ANSI 250	:	ing: Fan-cooled, surface cooling		
CONSTRUCTION: HPDESF E-coated ductile iron A536 Gr 120-90-2, stainles		 ure: -10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft) I/o: Two inputs, one output. Output can 		
MAXIMUM PUMP OPERATING CONDITIONS		be configured for voltage or current		
□ ANSI 125	Digital	I/o: Two inputs, two outputs. Outputs can be configured as inputs		
175 psig at 150°F (12 bar at 65°C)	Relay outp	uts: Two programmable		
100 psig at 250°F (7 bar at 121°C)	•	Communication port: 1-RS485		
☐ ANSI 250 300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)	of the system wide harmonics	** If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.		
MECHANICAL SEAL DESIGN DATA	: FLOW READOUT AC	CCURACY		

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

Stationary seat: Silicone carbide

Spring: Stainless steel

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

 $^{^\}star Only$ available if sensorless bundle is enabled

^{*}Available in single pump operation only

3




Performance curves are for reference only.


 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ADEPT}\ Quote\ or\ {\tt ADEPT}\ Select\ selection\ software.$


INDOOR

B1 B2 C2

OUTDOOR







DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)
Size:	1.5×1.5×3	1.5×1.5×3
Size:		
HP:	1	1
RPM:	3600	3600
AB:	17.14 (435)	19.35 (491)
В1:	4.90 (124)	4.90 (124)
B2:	4.90 (124)	4.90 (124)
C1:	10.00 (254)	10.00 (254)
C2:	10.00 (254)	10.00 (254)
CI:	_	5.00 (127)
D:	3.15 (80)	3.15 (80)
E:	8.20 (208)	8.62 (219)
s:	6.69 (170)	6.69 (170)
SD:	9.84 (250)	9.84 (250)
T:	3.54 (90)	3.54 (90)
Weight:	99 (44.9)	99 (44.9)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934