

# DESIGN ENVELOPE 4382 DUALARM | 0606-002.0 | SUBMITTAL

File No: 104.5503 Date: JULY 8, 2019 Supersedes: 104.5503 Date: AUGUST 1, 2018

Job:	Repres	sentative:		
	Order	No:	Date:	
Engineer:		tted by:	Date:	
Contractor: Appro		ved by:	Date:	
PUMP DESIGN DATA		CONTROLS DATA		
No. of pumps: Tag: Total system design flow:		Protocol (standard):	☐ BACnet <sup>™</sup> MS/TP ☐ BACnet <sup>™</sup> TCP/IP	
Head:ft(m) Capacity split _ Flow per pump head: Parallel flow:	% USgpm(L/s)	Enclosure:	☐ Modbus RTU ☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4x with Weather Shield	
Liquid: Viscosity:  Temperature: °F (°C) Specific gravity  Suction: 6" (150mm) Discharge: 6" (	r:	Fused disconnect switch:		
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified Test report is supplied with each pump			Integrated filter designed to meet EN61800-3 Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**	
MOTOR DESIGN DATA		Cooling:	Fan-cooled through back channel	
HP: RPM: Frame size: Enclosure: _ Hertz: 60 Hz Phase: 3 Efficiency: NEMA pre			-10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)	
MAXIMUM PUMP OPERATING CONDITANSI 125 - (CONSTRUCTION: BF)  175 psig at 150°F (12 bar at 65°C)	rions .	Digital ı/o: Pulse inputs:	Two current or voltage inputs, one speed output Two inputs, two outputs Two programmable Two programmable	
140 psig at 250°F (10 bar at 121°C)		Communication port:		
FLOW READOUT ACCURACY		guaranty performance to any sys	tem wide harmonic specification or the costs to	

#### MECHANICAL SEAL DATA

The Design Envelope model selected will provide flow reading

on the controls local keypad & digitally for the BMS. The model

readout will be factory tested to ensure ±5% accuracy.

Seal Type: 2A **Stationary Seat:** Silicon carbide Secondary Seal: EPDM Rotating Hardware: Stainless steel Spring: Stainless steel

FLUID TYPE	ALL GLYCOLS > 30%	6 WT CONC	ALL OTHER NON-POT	ABLE FLUIDS	POTABLE (DRINKIN	IG) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon	carbide	Resin bonded carbon	Antimony loaded carbon	Resin bond	ded carbon
Seat Elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

meet a system wide specification. If supplied with the system electrical details,

system harmonic levels are exceeded Armstrong can also recommend additional

Armstrong will run a computer simulation of the system wide harmonics. If

harmonic mitigation and the costs for such mitigation.

2

# **OPTIONS**

## SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

#### PARALLEL SENSORLESS (STANDARD)



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

#### ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

\*Only available if sensorless bundle is enabled

#### □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

# $\square$ ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

# □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Cooling

Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	

## **OPTIONAL SERVICES**

# **ON-SITE PUMP COMMISSIONING**



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

#### PUMP MANAGER




As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.

Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>The Service requires an active internet connection.

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

# INDOOR OUTDOOR SD D2 D1 D1 \_E1 B2 Ε B1 \_ E2\_ В1 В2 WEATHER ØΡ ØΡ SHIELD ΑВ

C1

C2

#### **DIMENSION DATA**

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	145	145
Size:	6×6×6	6×6×6
HP:	2	2
RPM:	1800	1800
AB:	12.65(321)	18.50(470)
B1:	7.39(188)	7.39(188)
B2:	7.39(188)	7.39(188)
C1:	13.63(346)	13.63(346)
C2:	14.31(364)	14.31(364)
D1:	16.81(427)	16.81(427)
D2:	16.81(427)	16.81(427)
E:	6.13(156)	6.13(156)
P:	8.63(219)	7.83(199)
F:	24.44(621)	30.40(772)
SD:	33.50(851)	33.50(851)
T:	7.75(197)	7.75(197)
XY:	17.25(438)	17.00(432)
Weight:	532(241.3)	540(244.9)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

#### BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

#### SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD. HONGKOU DISTRICT, SHANGHAI CHINA 200085 +86 (0) 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

